



LOC	DIST	P	F	ZONE		LTR	REVISIONS		DATE	APPD
							DESCRIPTION			
G	86					U	REV PER 0G3A-0561-01		090CT02	JR/MS



- 1 CIRCULAR MIL AREA RANGE: 375-450 MCM
- 2 TIN PL 0.00381 [.000150] MIN THK PER ASTM B-545
- 3 NO SIGHT HOLE



METRIC

				PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.51 [.020] 3 PLC DEC ± - ANGLES ± - MATERIAL ANNEALED COPPER ASTM B-75	DR 02/28/90 DK SCHRUM	AMP AMP INCORPORATED Harrisburg, Pa. 17105			
	CHK 23JAN95 MS FEHER				
	APPD 23JAN95 WJ VOCKROTH	NAME TERMINAL, AMPPOWER™ WIRE SIZE: 400 MCM			
APPD 23JAN95 TL SHUTTER					
PRODUCT SPEC 108-30200					
FINISH 2	APPLICATION SPEC -	SIZE C	CAGE CODE 00779	DRAWING NO 326807	
	WEIGHT .308 LB	SCALE 2:1	SHEET 1 OF 1		