

P/N S331AM-915


Alternative Connectors

.SMA Reverse Polarity Plug(female)

P/N: S331AH-915

.SMA Reverse Thread Plug(male)

P/N: S331AT-915



Electrical Properties:

Frequency Range: 902~928 MHz
Impedance: 50Ω nominal
VSWR: <2.0:1
Gain: 1 dBi
Radiation: Omni
Polarization: Vertical
Wave: 1/4 wave

Mechanical Properties:

Connector: SMA Plug
Material: Polyurethane-BASF(Black)
Whip: Brass with Chrome Plating(Black)
Connector: Brass with Chrome Plating(Black)
Operation Temp.: -20°C to +65°C
Storage Temp.: -30°C to +75°C

TOLERANCE		TITLE	900MHz ISM Band Antenna-331 Model		DATE	SHEET			
.X						1 OF 1			
.XX		UNIT	DWG. NO.	S331AM-915	A4				
.XXX		in.(mm)							
		SCALE	NEARSON						
ANGLE		1 : 1							