


8969-AB Series

Mini USB AB Type 10P SMD Female



Material:

Housing: High Temperature Plastic UL94V-0.

Contacts: Copper Alloy.

Shell: Metal.

Electrical Characteristics:

Current Rating: 1 A.

Dielectric Withstanding Voltage: AC 100V.

Insulator Resistance: 100MΩ min.




Contact Resistance: 50mΩ max.

Operating Temperature: -20°C~+85°C.




Features:

* Additional plating options available.

Mates with : 8970-AB10



P.C.Board Layout
Type 4



P.C.Board Layout
Type 5

Ordering information

8969-AB	10	G	10	D	4	B	T	-	S
Series	Position	G: Gold Plated	10: 10 μ"	D: SMD Type	4: Type 4 5: Type 5	B: Black	T: Tape & Reel Package		S: Mylar