


# METRIC AND PG THREAD LOCK NUTS

*Hexagonal Lock Nuts of nickel plated brass according to DIN 46320*

## TECHNICAL DETAILS:

**Material** Brass, Nickel Plated



## PG Thread Lock Nuts

| PG Metric Size | Part Number | Locknut Thickness (mm) | Wrenching Flats (mm) | Wrenching Flats (inches) |
|----------------|-------------|------------------------|----------------------|--------------------------|
| PG 7           | BSL-01      | 2.8                    | 15                   | .591                     |
| PG 9           | BSL-02      | 2.8                    | 18                   | .709                     |
| PG 11          | BSL-03      | 3.0                    | 21                   | .827                     |
| PG 13.5        | BSL-04      | 3.0                    | 23                   | .906                     |
| PG 16          | BSL-05      | 3.0                    | 26                   | 1.024                    |
| PG 21          | BSL-06      | 3.5                    | 32                   | 1.260                    |
| PG 29          | BSL-07      | 4.0                    | 41                   | 1.610                    |
| PG 36          | BSL-08      | 5.0                    | 51                   | 2.00                     |
| PG42           | BSL-09      | 5.0                    | 60                   | 2.364                    |
| PG48           | BSL-10      | 5.5                    | 64                   | 2.521                    |

## Metric Lock Nuts

| Metric Size | Metric Part Number | Locknut Thickness (mm) | Wrenching Flats (mm) | Wrenching Flats (inches) |
|-------------|--------------------|------------------------|----------------------|--------------------------|
| M12 X 1.5   | BMBL-01            | 2.8                    | 15                   | .591                     |
| M16 X 1.5   | BMBL-02            | 3.0                    | 19                   | .748                     |
| M20 X 1.5   | BMBL-03            | 3.5                    | 24                   | .945                     |
| M25 X 1.5   | BMBL-04            | 4.0                    | 30                   | 1.182                    |
| M32 X 1.5   | BMBL-05            | 5.0                    | 36                   | 1.418                    |
| M40 X 1.5   | BMBL-06            | 5.0                    | 46                   | 1.812                    |
| M50 X 1.5   | BMBL-07            | 5.0                    | 60                   | 1.970                    |
| M63 X 1.5   | BMBL-08            | 5.0                    | 70                   | 2.758                    |

Various colors, materials and sizes available upon request.

E-mail: [info@sabcable.com](mailto:info@sabcable.com)



Web site: [www.sabcable.com](http://www.sabcable.com)