

Steckerstifte

Fiches de goupille

Seamless pins

Werkstoff:

MS = Messing

Matière:

MS = laiton

Material:

MS = brass

Oberflächenbehandlung:

Code

bl = blank
ag = versilbert
au = vergoldet
ni = vernickelt
sn = verzinkt

(0)
(1)
(2)
(5)
(8)

Traitements de surface:

Code

bl = brut
ag = argenté
au = doré
ni = nickelé
sn = étamé

(0)
(1)
(2)
(5)
(8)

Surface-plating:

Code

bl = clean
ag = silver-plated
au = gold-plated
ni = nickel-plated
sn = tin-plated


(0)
(1)
(2)
(5)
(8)

Bestellbeispiel:


Exemple de commande:

Example of order:

1364A.68
(1364 A MS sn)



Print	Bohrung Trou Hole	D mm	L mm	T mm	L1 mm	D1 mm	B mm	Werkstoff Matière Material	Stand.- Packg. 2'000	Artikel-Nr. Numéro d'article Part-No.	Werkzeug Outils Tools
	Ø 1	9.5	2.4	6.6	Ø 1.8	1.05	MS	•		1364A.6()	1035/85
		10	3.5	6	Ø 1.8	1.05	MS	•		1364E.6()	1035/85
		14.1	3	10.6	Ø 1.8	1.05	MS	•		1364S.6()	1035/86
		10.8	4.5	5.8	Ø 1.8	1.05	MS	•		1364C.6()	1035/85
		11	4.5	6	Ø 1.8	1.05	MS	•		1364G.6()	1035/85
		11.5	3	8	Ø 1.8	1.05	MS	•		1364B.6()	1035/86
		12.5	5	7	Ø 1.8	1.05	MS	•		1364F.6()	1035/85
		15.5	3	12	Ø 1.8	1.05	MS	•		1364D.6()	1035/86
		20	3.5	16	Ø 1.8	1.05	MS	5000		1364T.6()	1035/86
		18	6	11.5	Ø 1.8	1.05	MS	•		1364R.6()	1035/86
	Ø 1.3	11	4.5	6	Ø 2.5	1.4	MS	1000		1365A.6()	1035/84
		12.5	3.8	8.1	Ø 2.5	1.4	MS	1000		1365F.6()	1035/83
		13.5	5	8	Ø 2.5	1.4	MS	1000		1365B.6()	1035/83
		13.5	5.5	7.5	Ø 2.5	1.4	MS	1000		1365C.6()	1035/83
		14.7	2.5	11.7	Ø 2.5	1.4	MS	1000		1365D.6()	1035/83
		15.9	5.7	9.7	Ø 2.5	1.4	MS	1000		1365E.6()	1035/83
		16	3	12.5	Ø 2.5	1.4	MS	1000		1365M.6()	1035/83
	Ø 1.33	9.5	3.5	5.5	Ø 2.5	1.43	MS	•		1365.6()	1035/84



D mm	L mm	T mm	L1 mm	D1 mm	B mm	Werkstoff Matière Material	Stand.- Packg. 1'000	Artikel-Nr. Numéro d'article Part-No.	Werkzeug Outils Tools
Ø 1	10	3.5	6	Ø 1.8	Ø 1	MS	•	1364P.6()	1035/85
	11	4.5	6	Ø 1.8	Ø 1	MS	•	1364K.6()	1035/85
	15	8.5	6	Ø 1.8	Ø 1	MS	•	1364M.6()	1035/85
	15.4	6	8.9	Ø 1.8	Ø 1	MS	•	1364H.6()	1035/86
	15.4	9	5.9	Ø 1.8	Ø 1	MS	•	1364L.6()	1035/85
Ø 1.3	16.2	5.9	9.8	Ø 2.5	Ø 1.3	MS	•	1365L.6()	1035/83

Andere Abmessungen auf Anfrage
Autres dimensions sur demande
Further dimensions on request