



ALLEN HEX STANDARD TIP AND BALLPOINT TIP SCREWDRIVERS

Precision-formed, alloy steel blades. Shockproof, breakproof, amber plastic handles. Unique ballpoint tip makes these Xcelite drivers ideal for tightening and removing Allen type socket head screws in spots where you can't reach them straight-on.

Cat. No.	Hex Size	Blade Length	Handle Dims.	Overall Length	Net Price
STANDARD TIP					
LN20	.050"	4"	7/8" x 2 5/8"	6 5/8"	\$6.51
LN21	1/16"	4"	7/8" x 2 5/8"	6 5/8"	6.51
LN22	5/64"	4"	7/8" x 2 5/8"	6 5/8"	6.51
LN23V	3/32"	4"	1 1/16" x 3 1/8"	7 1/8"	6.51
LN764	7/64"	4"	1 1/16" x 3 1/8"	7 1/8"	6.57
LN24	1/8"	4"	1 1/16" x 3 1/8"	7 1/8"	6.99
LN964	9/64"	4"	1 1/16" x 3 1/8"	7 1/8"	7.07
LN25	5/32"	6"	1 1/16" x 3 1/8"	9 1/8"	6.99
LN26	3/16"	6"	1 1/8" x 4 1/8"	10 1/8"	6.99
LN27	7/32"	6"	1 1/8" x 4 1/8"	10 1/8"	7.80

Cat. No.	Hex Size	Blade Length	Handle Dims.	Overall Length	Net Price
BALLPOINT TIP					
LN20BP	.050"	4"	7/8" x 2 5/8"	6 5/8"	\$10.14
LN21BP	1/16"	4"	7/8" x 2 5/8"	6 5/8"	10.14
LN22BP	5/64"	4"	7/8" x 2 5/8"	6 5/8"	10.14
LN23BP	3/32"	4"	1 1/16" x 3 1/8"	7 1/8"	10.14
LN764BP	7/64"	4"	1 1/16" x 3 1/8"	7 1/8"	10.25
LN24BP	1/8"	4"	1 1/16" x 3 1/8"	7 1/8"	10.58
LN964BP	9/64"	4"	1 1/16" x 3 1/8"	7 1/8"	10.68
LN25BP	5/32"	4"	1 1/16" x 3 1/8"	7 1/8"	10.58
LN26BP	3/16"	4"	1 1/8" x 3 1/8"	7 1/8"	10.58
LN28BP	1/4"	4"	1 1/8" x 3 1/8"	7 1/8"	11.00
LN11	A complete set of 11 Standard Tip Drivers with amber handles. Sizes shown in table above. Comes in a roll-up canvas case, plastic coated for wear protection.				74.10
LN9BP	A complete set of 9 Ballpoint Tip Drivers (LN20BP through LN28BP) with amber handles. Sizes shown in table above. Comes in a roll-up canvas case, plastic coated for wear protection.				90.20



"SUPER-TRU" PRECISION DRIVERS WITH BLACK OXIDE TIP

The nickel chrome blades have tips which are treated and finished with black oxide to give a closer fit with the screw, giving longer life and less damage to the head recess. Shockproof, breakproof, black plastic handles are shaped for perfect grip and balance.


Cat. No.	Point Size	Blade Dia.	Blade Length	Handle Dims.	Overall Length	Net Price
XST100V	0	1/8"	2"	7/8" x 2 5/8"	4 5/8"	\$5.40
XST101V	1	3/16"	3"	1" x 3 3/8"	6 5/8"	7.52
XST102V	2	1/4"	4"	1 1/8" x 4 1/8"	8 1/8"	9.56
XST1010	1	3/16"	10"	1" x 3 3/8"	13 3/8"	11.36
XST1020	2	1/4"	10"	1 1/8" x 4 1/8"	14 1/8"	12.68
XST3	"SUPER-TRU" kit of 3 Phillips screwdrivers #0, 1, 2 in see-thru pouch.					22.71
XST5	"SUPER-TRU" kit of 5 Phillips screwdrivers #0, 1, 2 and #1, 2, 10" blade in see-thru pouch.					47.00



ALLEN HEX STANDARD TIP AND BALLPOINT TIP METRIC SCREWDRIVERS

Precision-formed, alloy steel blades. Shockproof, breakproof, black plastic handles. Unique ballpoint tip makes these Xcelite drivers ideal for tightening and removing Allen type socket head screws in spots where you can't reach them straight-on.

Cat. No.	Hex Size mm	Blade Length mm	Handle Dims. mm x mm	Overall Length mm	Net Price
STANDARD TIP					
LN127MM	1.27	101.60	22.22 x 66.67	168.27	\$8.46
LN15MM	1.50	101.60	22.22 x 66.67	168.27	7.77
LN2MM	2.00	101.60	22.22 x 66.67	168.27	8.46
LN25MM	2.50	101.60	26.99 x 79.38	180.97	8.28
LN3MM	3	101.60	26.99 x 79.38	180.97	9.11
LN4MM	4	101.60	26.99 x 79.38	180.97	9.11
LN5MM	5	101.60	26.99 x 79.38	180.97	9.11
LN6MM	6	101.60	26.99 x 79.38	180.97	11.16
BALLPOINT TIP					
LN127MMBP	1.27	101.60	22.22 x 66.67	168.27	11.16
LN15MMBP	1.50	101.60	22.22 x 66.67	168.27	11.16
LN2MMBP	2.00	101.60	22.22 x 66.67	168.27	11.16
LN25MMBP	2.50	101.60	26.99 x 79.38	180.97	10.38
LN3MMBP	3	101.60	26.99 x 79.38	180.97	11.63
LN4MMBP	4	101.60	26.99 x 79.38	180.97	11.63
LN5MMBP	5	101.60	26.99 x 79.38	180.97	11.36
LN6MMBP	6	101.60	26.99 x 79.38	180.97	11.82
LN8MM	A complete set of 8 Standard Tip Metric Drivers with black handles. Size shown in table above. Comes in a roll-up canvas case, plastic coated for wear protection.				70.11
LN8MMBP	A complete set of 8 Ballpoint Tip Metric Drivers with black handles. Sizes shown in table above. Comes in a roll-up canvas case, plastic coated for wear protection.				91.92




TA2

MIDGET ALLEN HEX TYPE SCREWDRIVERS IN INCH AND METRIC SIZES

These Allen hex type screwdrivers are sold separately or in sets. Each set comes complete with TA2 "Piggyback" torque amplifier handle that slips over the midget handles to provide larger gripping surface, extended reach, and increased driving power; slim, trim see-thru plastic case fits pocket or sits flat on work bench.

Cat. No.	Hex Sizes	Overall Length	Net Price
P18	.028"	4"	\$3.72
P19	.035"	4"	3.72
P20	.050"	4"	3.72
P21	1/16"	4"	3.72
P22	5/64"	4"	3.72
P23	3/32"	4"	3.72
TA2	Hollow torque amplifier handle. Sold separately for tools in table above. Colour black.		3.38
PS89V	A complete set of 8 Standard Inch size hex screwdrivers with red handles. Sizes shown in table above.		35.42
PS90MM	A complete set of 8 Metric hex screwdrivers with black handles. Sizes: 0.89 mm, 1.27 mm, 1.5 mm, 2.0 mm, 2.5 mm, 3.0 mm, 4.0 mm and 5.0 mm.		40.08



147TB



HS618



SUPER LONG

COLOUR CODED HOLLOW SHAFT NUTDRIVERS

These general purpose nutdrivers are especially useful where nuts must be installed or removed over long protruding bolts or studs. Shafts are steel and have precision, cold drawn, case-hardened sockets. Shockproof, breakproof, firm grip, plastic handles are color coded and marked with large, readable sizes.

Cat. No.	Colour Code	Hex Opening	Depth Of Hole	Blade Length	Handle Dims.	Overall Length	Net Price
REGULAR							
HS6V	Black	3/16"	6"	3 1/8"	1 1/16" x 3 1/8"	6 1/4"	\$7.31
HS7V	Brown	7/32"	6"	3 1/8"	1 1/16" x 3 1/8"	6 1/4"	7.31
HS8V	Red	1/4"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	7.31
HS9V	Orange	9/32"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	7.31
HS10V	Amber	5/16"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	7.31
HS11V	Green	11/32"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	7.74
HS12V	Blue	3/8"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	7.74
HS14V	Brown	7/16"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	9.99
HS16V	Red	1/2"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	9.99
HS18V	Orange	9/16"	7"	3 1/8"	1 1/8" x 4 1/8"	7 1/4"	9.99
L—EXTRA LONG AND LL—SUPER LONG							
L6	Black	3/16"	8 3/4"	6"	1 1/16" x 3 1/8"	9 1/8"	9.03
L8V	Red	1/4"	9 3/4"	6"	1 1/8" x 4 1/8"	10 1/8"	9.03
L8MV*	Red	1/4"	—	6"	1 1/8" x 4 1/8"	10 1/8"	12.99
LL8M*	Red	1/4"	—	16 3/4"	1 1/8" x 4 1/8"	20 7/8"	28.92
L10	Amber	5/16"	9 3/4"	6"	1 1/8" x 4 1/8"	10 1/8"	9.03
L10MV*	Amber	5/16"	—	6"	1 1/8" x 4 1/8"	10 1/8"	12.99
LL10M*	Amber	5/16"	—	16 3/4"	1 1/8" x 4 1/8"	20 7/8"	28.92
L11	Green	11/32"	9 3/4"	6"	1 1/8" x 4 1/8"	10 1/8"	9.51
L12V	Blue	3/8"	9 3/4"	6"	1 1/8" x 4 1/8"	10 1/8"	9.51
HS618	A set of 10 Nutdrivers HS6 to HS18. Sturdy yellow plastic case keeps nutdrivers orderly on workbench, carries them on service calls.						65.60
147TB	A set of 7 Nutdrivers HS8, HS9, HS10, HS11, HS12, HS14 and HS16. Sturdy Black plastic bench tray has provision for wall mounting.						56.63
177	A set of 7 Nutdrivers HS6, HS8, HS10, HS11, HS12, HS14 and HS16. Plastic see-thru carrying pouch for tool box or workbench.						56.63

*Magnetic Nutdrivers. Alnico permanent magnet in socket holds fasteners firmly for easy, one-hand driving or for retrieving on removal. Socket itself is insulated from magnet to prevent deflection by nearby metal surfaces.



SOLID AND HOLLOW SHAFT METRIC SIZE NUTDRIVERS

Manufactured precisely to metric dimensions, these tools are particularly useful in the assembly and servicing of foreign equipment. Shafts are finished in bright nickel chrome. Black handles.

Cat. No.	Hex Opening mm	Depth Of Hole mm	Blade Length mm	Handle Dims. mm x mm	Overall Length mm	Net Price
SOLID SHAFT REGULAR						
4MM	4	28.58	76.20	25.4 x 79.38	155.58	\$7.20
45MM	4.5	28.58	76.20	25.4 x 79.38	155.58	7.83
5MM	5	28.58	76.20	25.4 x 79.38	155.58	7.20
55MM	5.5	28.58	76.20	25.4 x 79.38	155.58	7.20
6MM	6	28.58	76.20	25.4 x 79.38	155.58	7.83
7MM	7	28.58	76.20	25.4 x 79.38	155.58	7.20
8MM	8	28.58	76.20	25.4 x 79.38	155.58	7.20
10MM	10	47.63	73.02	26.99 x 104.78	177.80	8.84
11MM	11	47.63	73.02	26.99 x 104.78	177.80	9.62
HOLLOW SHAFT REGULAR						
12MM	12	177.80	79.38	28.58 x 104.78	184.15	11.94
13MM	13	177.80	79.38	28.58 x 104.78	184.15	11.94
413MM	A set of 10 Metric nutdrivers 4MM through 8MM, 10MM, 11MM and 13MM. Sturdy red plastic 'keep and carry' case, keeps nutdrivers orderly on workbench, carries them on service calls.					83.27




TA2

MIDGET NUTDRIVERS IN INCH AND METRIC SIZES

Midget Nutdrivers are sold separately or in sets. Each set comes complete with TA2 "Piggyback" torque amplifier handle that slips over the midget handles to provide large gripping surface, extended reach, and increased driving power; slim, trim see-thru plastic case fits pocket or sits flat on work bench.

Cat. No.	Hex Opening	Overall Length	Net Price
P4	1/8"	3 1/2"	\$4.38
P5	5/32"	3 1/2"	4.38
P6	3/16"	3 1/2"	4.38
P8	1/4"	3 1/2"	4.38
P10	5/16"	3 1/2"	4.38
TA2	Hollow torque amplifier handle. Sold separately for tools in table above. Colour black.		3.38
PS120V	A complete set of 10 Inch size nutdrivers with color coded handles. Sizes shown in table above.		47.79
PS121MM	A complete set of 10 Metric size nutdrivers with black handles. Sizes: 3 mm, 3.5 mm, 4 mm, 4.5 mm, 5 mm, 5.5 mm, 6 mm, 7 mm, 8 mm, and 10 mm.		58.94



SERIES 99 HANDLES AND INTERCHANGEABLE BLADES

The series 99 interchangeable blades and handles are all available separately, allowing gradual, economical accumulation of whatever items might be needed for your individual requirements. This also permits owners of series 99 sets or kits to enlarge them or substitute tools, as necessary, at minimal cost. All blades are high carbon steel with highly polished nickel chrome finish except Bristol and Allen hex types which are precision formed, cold drawn, case hardened steel. Plastic handles have a patented spring device that holds blades firmly, yet permits quick, easy insertion and removal. All the 99 series blades fit all the 99 series handles.


Cat. No.	Description	Net Price
991	1" x 4 1/2" Regular handle. Colour Amber	\$5.78
992	1" x 3 1/8" Junior handle. Colour Amber	5.60
993	1" x 2" Stubby handle. Colour Amber	5.54
994V	3 1/2" x 1 1/8" Tee handle. Colour Black	7.56



RATCHET HANDLES

The 99 series Reversible Ratcheting Handles, which permits extremely simple one-hand operation, even in tight quarters. The recessed reversing shift is easily operated by the thumb, yet cannot be accidentally tripped by the palm while driving.


Cat. No.	Description	Net Price
994R	3 1/2" x 2 5/8" Tee ratchet handle. Colour Black	\$39.12



99 SERIES POWER BIT

Power bit Adapter for 99 Series. Fits all Power Tools with 1/4" chuck.

Cat. No.	Net Price
99PAV	\$7.46



ALLEN HEX


Unique ballpoint tip makes these Xcelite drivers ideal for tightening and removing Allen type socket head screws in spots where you can't reach them straight-on.

INCH SIZES

Cat. No.	Hex Size	Approx. Working Length	Net Price
STANDARD TIP			
9920	.050"	4"	\$4.92
9921	1/16"	4"	4.92
9922	3/64"	4"	4.92
9923	3/32"	4"	4.92
99764	7/64"	4"	4.92
9924	1/8"	4"	4.92
99964	9/64"	4"	4.92
9925	5/32"	4"	4.92
9926	3/16"	4"	4.92
BALLPOINT TIP			
9920BP	.050"	4"	9.11
9921BP	1/16"	4"	8.36
9922BP	3/64"	4"	8.36
9923BP	3/32"	4"	8.36
99764BP	7/64"	4"	8.36
9924BP	1/8"	4"	8.36
99964BP	9/64"	4"	8.36
9925BP	5/32"	4"	8.36
9926BP	3/16"	4"	8.36
99PS40V	A complete set of 7 Standard tip Metric drivers in see-thru plastic case. Sizes shown in table above. Regular handle and Extension blade included.		52.57
99PS40BPV	A complete set of 9 Ballpoint tip drivers in see-thru plastic case. Sizes shown in table above. Regular handle and Extension blade included.		88.79

METRIC SIZES


Cat. No.	Hex Sizes	Approx. Working Length	Net Price
9971MM	1.27	101.60	\$6.30
9972MM	1.5	101.60	6.30
9973MM	2	101.60	6.30
9974MM	2.5	101.60	6.30
9975MM	3	101.60	6.30
9976MM	4	101.60	6.30
9977MM	5	101.60	6.30
99PS41MM	A complete set of 7 Standard tip Metric drivers in see-thru plastic case. Sizes shown in table above. Regular handle and Extension blade included.		58.16
99PS41MMBP	A complete set of 7 Ballpoint tip Metric drivers in see-thru plastic case. Sizes shown in table above. Regular handle and Extension blade included.		72.32



SERIES 99 NUTDRIVER/SCREWDRIVER SET

Pocket size plastic see-thru case packs an unusual number of tools into a small space. Flat bottom of case permits its use as bench stand. This set consists of 7 nutdrivers (3/16" thru 3/8"), 2 slotted screwdrivers (3/16" and 1/4"), and 2 Phillips screwdrivers (#1 and #2). Regular handle and Extension blade included.

Cat. No.	Net Price
99PS50V	\$74.37



NUTDRIVERS

Cat. No.	Description	Approx. Working Length	Net Price
REGULAR NUTDRIVERS			
996	3/16" Nutdriver	3 3/8"	\$6.46
997V	7/32" Nutdriver	3 3/8"	5.54
998	1/4" Nutdriver	3 3/8"	6.46
998M*	1/4" Magnetic Nutdriver	3 3/8"	7.65
999	9/32" Nutdriver	3 3/8"	5.34
9910	5/16" Nutdriver	3 3/8"	6.46
9911	11/32" Nutdriver	3 3/8"	6.70
9912	3/8" Nutdriver	3 3/8"	6.70
9914	7/16" Nutdriver	4"	7.40
9916V	1/2" Nutdriver	4"	7.40
METRIC NUTDRIVERS			
994MM	4mm Nutdriver	92.08mm	6.24
9945MM	4.5mm Nutdriver	92.08mm	6.24
995MM	5mm Nutdriver	92.08mm	6.24
9955MM	5.5mm Nutdriver	92.08mm	6.24
996MM	6mm Nutdriver	92.08mm	6.24
997MM	7mm Nutdriver	92.08mm	6.24
998MM	8mm Nutdriver	92.08mm	6.24
999MM	9mm Nutdriver	92.08mm	8.33
9910MM	10mm Nutdriver	101.60mm	8.33
9911MM	11mm Nutdriver	101.60mm	7.65
99PS51MM	A complete set of 10 Metric nutdrivers in plastic see-thru case. Sizes shown in table above. Regular handle and Extension blade included.		93.42

*Magnetic Nutdrivers. Alnico permanent magnet in socket holds fasteners firmly for easy, one-hand driving or for retrieving on removal. Socket itself is insulated from magnet to prevent deflection by nearby metal surfaces.



SLOTTED

Cat. No.	Description	Approx. Working Length	Net Price
99125	1/8" Slotted screwdriver	3 3/8"	\$5.54
99811V	3/16" Slotted screwdriver	3 3/8"	5.54
99250V	1/4" Slotted screwdriver	3 3/8"	5.54
99312	5/16" Slotted screwdriver	3 3/8"	5.54



PHILLIPS

Cat. No.	Description	Approx. Working Length	Net Price
99820V	No. 0 Phillips screwdriver	3 3/8"	\$5.54
99821V	No. 1 Phillips screwdriver	3 3/8"	5.54
99822V	No. 2 Phillips screwdriver	3 3/8"	5.54



POSIDRIV

Cat. No.	Description	Approx. Working Length	Net Price
99831	No. 1 Posidriv screwdriver	3 3/8"	\$9.23
99832	No. 2 Posidriv screwdriver	3 3/8"	9.23



TORX

Cat. No.	Description	Approx. Working Length	Net Price
996XTD	No. T6 Torx	4"	\$6.08
998XTD	No. T8 Torx	4"	6.08
9910XTD	No. T10 Torx	4"	6.08
9915XTD	No. T15 Torx	4"	6.08
9920XTD	No. T20 Torx	4"	6.08
9925XTD	No. T25 Torx	4"	6.08
9927XTD	No. T27 Torx	4"	6.08
9930XTD	No. T30 Torx	4"	6.08



EXTENSIONS

Cat. No.	Description	Approx. Working Length	Net Price
99X5	Extension blade (adds 4" reach to blades).	4"	\$8.82
99X10V	Extension blade (adds 7" reach to blades).	7"	8.21



REAMER

Cat. No.	Description	Approx. Working Length	Net Price
9938	1/8" to 3/8" Reamer	4 1/2"	\$14.15



SERIES 99 SERVICE KITS

These space-saving kits contain popular Series 99 plastic handles and interchangeable screwdriver and nutdriver blades. Durable, roll-up cases of tough plastic won't mar any surface they're placed on.

MULTI-PURPOSE TOOL KIT

All the most popular Series 99 tools are readily available in this convenient 39-piece kit. Plastic coated canvas case folds into a compact, easy-to-carry package which is quickly and positively secured by means of a permanently attached elastic loop. No tying required. Two extra pockets permit addition of pliers, snips or other tools. Kit includes regular (1" x 4 1/2") and Tee (3 1/2" x 1 1/2") plastic handles and following interchangeable blades: 9 regular nutdrivers (3/16" thru 1/2") and 1 Magnetic nutdriver (1/4"), 9 Allen hex screwdrivers (.050" thru 3/16"), 9 Bristol Multiple-Spline screwdrivers (.048" thru .183"), 4 slotted screwdrivers (1/8", 3/16", 1/4" and 5/16"), 3 Phillips screwdrivers (#0, #1 and #2), (1/8" to 3/8") reamer and 4" extension blade.

Cat. No.	Description	Net Price
99MP	Kit	\$253.83
99MPK	Case only for 99MP	35.24



METRIC HARDWARE ASSORTMENT

Contains Round Head Machine Screws. Hex Nuts. Flat Washer and Spring Lock Washer, in Steel, Nickel Plated. Comes in 2, 2.6, 3, 4, and 5 mm sizes. Total quantity 560 pieces.

Cat. No.	Net Price
11-528	\$62.88



NYLON HARDWARE ASSORTMENT

Contents	Thickness	Qty. in Pkg.
ROUND HEAD MACHINE SCREWS		
#6-32 x 1/2"		10
#6-32 x 1/2"		10
BINDING HEAD MACHINE SCREWS		
#6-32 x 1/2"		10
#8-32 x 1/2"		10
HEX NUTS		
#6-32 x 5/16"	7/16"	20
#8-32 x 1/2"	1/8"	20

Screw Size	Hole Size	O.D.	Thickness	Qty. in Pkg.
WASHERS				
#6	.150"	5/16"	.050"	20
#8	.170"	3/8"	.050"	20

Cat. No.	Net Price
11-516	\$14.65



11-510

FUSE CLIPS

For easy replacement of fuses on PC boards. Clips fit standard 1/4" diameter fuses.

Cat. No.	Type	Pkg. Qty.	Net Price
11-510	Pigtail	12	\$4.09



HOLE PLUGS

Nickel plated steel snap-in hole plugs.

Cat. No.	Description	Net Price
11-344-C	1/4" Dia. hole plugs	\$21.11
11-392-C	1" Dia. Vent hole plugs	130.20




FLAT METAL WASHERS STEEL, NICKEL PLATED

Cat. No.	Description				Net Price
	Screw Size	Hole Size	O.D.	Thick-ness	
11-142-C	#4	1/8"	9/32"	1/32"	\$3.39
11-146-C	#6	5/32"	3/8"	1/32"	3.46

FLAT FIBRE WASHERS

11-428-C	#4	.120"	1/4"	1/32"	3.92
11-432-C	#6	5/64"	1/4"	1/32"	4.06



G-C INSULATING CAMBRIC "BREAKDOWN VOLTAGE 5,000 VOLTS"

Dry yellow varnished cambric for field coils, transformers, chokes, resistors, motors, etc. Needed for many repair jobs to insulate parts and wires. Width 9 inches.

Cat. No.	Description	Net Price
00-0549-0000	.010"-Roll, 210 sq. in.	\$5.83



Part's indicated with a leaf  are considered RoHS July 2006 compliant based on the manufacturer's confirmation at the time of publishing. For additional information please contact Electro Sonic.