

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 22-05-2121
Status: Active
Overview: KK® Interconnect System - Molex
Description: KK® 254 Wire-to-Board Header, Single Row, Right Angle, 12 Circuits, PA Polyamide Nylon, Tin (Sn) Plating

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)

[Product Specification PS-10-07 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Headers
Series 4094
Application Board-to-Board, Signal, Wire-to-Board
Overview KK® Interconnect System - Molex
Product Name KK® 254
UPC 800753591110

Physical

Breakaway No
Circuits (Loaded) 12
Circuits (maximum) 12
Color - Resin Natural (White)
Durability (mating cycles max) 25
Flammability 94V-0
Glow-Wire Compliant No
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Resin Nylon
Net Weight 0.968/g
Number of Rows 1
Orientation Right Angle
PC Tail Length 3.15mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Bag
Pitch - Mating Interface 2.54mm
Pitch - Termination Interface 2.54mm
Polarized to Mating Part No
Polarized to PCB No
Shrouded No
Stackable Yes
Surface Mount Compatible (SMC) No
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 4A
Voltage - Maximum 250V

Solder Process Data



image - Reference only

Series

EU RoHS
ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
4094Series

Mates With
2695 , 6471 , 7880 , 4455 , 7720

Duration at Max. Process Temperature (seconds)	5
Lead-free Process Capability	Wave Capable (TH only)
Max. Cycles at Max. Process Temperature	1
Process Temperature max. C	235

Material Info

Old Part Number	A-4094-12A197
-----------------	---------------

Reference - Drawing Numbers

Product Specification	PS-10-07
Sales Drawing	SDA-4094

This document was generated on 07/08/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[22-05-2121](#)