



CUSTOM CONNECTOR CORPORATION

# Relay Sockets

•UL recognized, File No. E60008

•CSA certified, File No. LR29513



| Mfr.'s Type | Description                 | Terminal Type         |
|-------------|-----------------------------|-----------------------|
| RB08        | DPDT, 8 Pin Octal (Fig. 1)  | Binder Head Screws    |
| RB08-PC     | DPDT, 8 Pin Octal (Fig. 1)  | Pressure Clamp Screws |
| RB11        | 3PDT, 11 Pin Octal (Fig. 2) | Binder Head Screws    |
| RB11-PC     | 3PDT, 11 Pin Octal (Fig. 2) | Pressure Clamp Screws |

ELECTRICAL RATING: • RB08, RB08-PC - 600 Volts, 10 Amps  
• RB11, RB11-PC - 300 Volts, 10 Amps

Fig. 1





Fig. 2



| Mfr.'s Type | Description                       | Terminal Type |
|-------------|-----------------------------------|---------------|
| OB08-PCB    | DPDT, 8 Pin Octal (Fig. 1)        | PC Board      |
| OB11-PCB    | 3PDT, 11 Pin Octal Style (Fig. 2) | PC Board      |

ELECTRICAL RATING: • 300 Volts, 10 Amps

Fig. 1






Fig. 2



| Mfr.'s Type | Description         | Terminal Type         |
|-------------|---------------------|-----------------------|
| QC08        | DPDT, 8 Pin Square  | Binder Head Screws    |
| QC08-PC     | DPDT, 8 Pin Square  | Pressure Clamp Screws |
| QC11        | 3PDT, 11 Pin Square | Binder Head Screws    |
| QC11-PC     | 3PDT, 11 Pin Square | Pressure Clamp Screws |

ELECTRICAL RATING: • 300 Volts, 10 Amps • 150 Volts, 15 Amps




ACCESSORY

HDB-3 ..... Hold Down Spring



| Mfr.'s Type | Description         | Terminal Type         |
|-------------|---------------------|-----------------------|
| SS08        | DPDT, 8 Pin Square  | Binder Head Screws    |
| SS08-PC     | DPDT, 8 Pin Square  | Pressure Clamp Screws |
| SS11        | 3PDT, 11 Pin Square | Binder Head Screws    |
| SS11-PC     | 3PDT, 11 Pin Square | Pressure Clamp Screws |

ELECTRICAL RATINGS: • 300 Volts, 10 Amps • 150 Volts, 15 Amps



ACCESSORY

HDB-8 ..... Hold Down Spring



| Mfr.'s Type | Description     | Terminal Type         |
|-------------|-----------------|-----------------------|
| SD12        | 12 Pin (Fig. 1) | Binder Head Screws    |
| SD12-PC     | 12 Pin (Fig. 1) | Pressure Clamp Screws |
| SD14        | 14 Pin (Fig. 2) | Binder Head Screws    |
| SD14-PC     | 14 Pin (Fig. 2) | Pressure Clamp Screws |

ELECTRICAL RATINGS: • SD12, SD14 - 600 Volts, 10 Amps  
• All others - 300 Volts, 10 Amps

Fig. 1





Fig. 2








CUSTOM CONNECTOR CORPORATION

# Relay Sockets

- ULrecognized, File No. E60008
- CSAcertified, File No. LR29513



| Mfr.'s Type | Description                  | Terminal Type    |
|-------------|------------------------------|------------------|
| CM08-SLD    | DPDT, 8 Pin Square (Fig. 2)  | Solder           |
| CM08-QDC    | DPDT, 8 Pin Square (Fig. 1)  | Quick Disconnect |
| CM11-SLD    | 3PDT, 11 Pin Square (Fig. 2) | Solder           |
| CM11-QDC    | 3PDT, 11 Pin Square (Fig. 1) | Quick Disconnect |

ELECTRICALRATING: • 300 Volts, 10 Amps • 150 Volts, 15 Amps

ACCESSORY

HDB-5 ..... Hold Down Spring



Fig. 1





Fig. 2



| Mfr.'s Type  | Description                                 | Terminal Type |
|--------------|---------------------------------------------|---------------|
| CM08-PCB-1S  | DPDT, 8 Pin Square, No Mount Ends (Fig. 2)  | PC Board      |
| CM08-PCB     | DPDT, 8 Pin Square (Fig. 1)                 | PC Board      |
| CM08-LPCB-1S | DPDT, 8 Pin Square, No Mount Ends (Fig. 2)  | Long PC Board |
| CM08-LPCB    | DPDT, 8 Pin Square (Fig. 1)                 | Long PC Board |
| CM11-PCB-1S  | 3PDT, 11 Pin Square, No Mount Ends (Fig. 2) | PC Board      |
| CM11-PCB     | 3PDT, 11 Pin Square (Fig. 1)                | PC Board      |
| CM11-LPCB-1S | 3PDT, 11 Pin Square, No Mount Ends (Fig. 2) | Long PC Board |
| CM11-LPCB    | 3PDT, 11 Pin Square (Fig. 1)                | Long PC Board |

ELECTRICALRATING: • 300 Volts, 10 Amps • 150 Volts, 15 Amps

ACCESSORY

HDB-5 ..... Hold Down Spring



| Mfr.'s Type   | Description                     | Terminal Type                |
|---------------|---------------------------------|------------------------------|
| MR08-PCB      | DPDT, 8 Pin Miniature (Fig. 1)  | PC Board                     |
| MR08-PCB-1G   | DPDT, 8 Pin Miniature (Fig. 1)  | PC Board, Ground Lug Omitted |
| MR08-PCB-1G N | DPDT, 8 Pin Miniature (Fig. 3)  | PC Board                     |
| MR08-SLD      | DPDT, 8 Pin Miniature (Fig. 2)  | Solder                       |
| MR08-SLD-1G   | DPDT, 8 Pin Miniature (Fig. 2)  | Solder, Ground Lug Omitted   |
| MR14-PCB      | 4PDT, 14 Pin Miniature (Fig. 1) | PC Board                     |
| MR14-PCB-1G   | 4PDT, 14 Pin Miniature (Fig. 1) | PC Board, Ground Lug Omitted |
| MR14-PCB-1G N | 4PDT, 14 Pin Miniature (Fig. 3) | PC Board                     |
| MR14-SLD      | 4PDT, 14 Pin Miniature (Fig. 2) | Solder                       |
| MR14-SLD-1G   | 4PDT, 14 Pin Miniature (Fig. 2) | Solder, Ground Lug Omitted   |

ELECTRICALRATING: • 300 Volts, 5 Amps

ACCESSORY

HDB-4 ..... Hold Down Spring

HDB-9 ..... Hold Down Spring







Fig. 3



| Mfr.'s Type | Description                 | Terminal Type         |
|-------------|-----------------------------|-----------------------|
| GR108-PCB   | DPDT, 8 Pin Midget (Fig. 2) | PC Board              |
| GR108-SLD   | DPDT, 8 Pin Midget (Fig. 3) | Solder                |
| GR108-PC    | DPDT, 8 Pin Midget (Fig. 1) | Pressure Clamp Screws |

ELECTRICALRATING: • GR108-PCB & SLD - 300 Volts, 10 Amps  
• GR108-PC - 300 Volts, 10 Amps  
150 Volts, 15 Amps

ACCESSORY

HDB-4 ..... Hold Down Spring

HDB-9 ..... Hold Down Spring

Fig. 1




Fig. 2





Fig. 3








CUSTOM CONNECTOR CORPORATION



# Relay Sockets

UL recognized, File No. E113714  
CSA certified, File No. LR26716





| Mfr.'s Type | Description                | Terminal Type |
|-------------|----------------------------|---------------|
| ES8         | DPDT, 8 Pin Octal (Fig. 1) | Box Lug       |
| ES11        | 3PDT, 8 Pin Octal (Fig. 2) | Box Lug       |

ELECTRICAL RATING: • 300 Volts, 10 Amps

## ACCESSORY

HDB-13 ..... Hold Down Spring  
T ..... Marking Plate



| Mfr.'s Type | Description            | Terminal Type         |
|-------------|------------------------|-----------------------|
| ES15/4      | 4PDT, 14 Pin Miniature | Pressure Clamp Screws |

ELECTRICAL RATING: • 300 Volts, 7 Amps

## ACCESSORY

MHO ..... Hold Down Spring  
Plug-in indicator and protection modules available

Fig. 1





Fig. 2






| Mfr.'s Type | Description                    | Terminal Type |
|-------------|--------------------------------|---------------|
| ES35        | SPDT, 5 Pin Slim Line (Fig. 1) | Box Lug       |
| ES50        | DPDT, 8 Pin Slim Line (Fig. 2) | Box Lug       |

ELECTRICAL RATING: • 300 Volts, 12 Amps

## ACCESSORY

MH12-2 ..... Hold Down Spring  
MH16-2 ..... Hold Down Spring  
MH25-2 ..... Hold Down Spring  
Plug-in indicator and protection modules available



| Mfr.'s Type | Description                    | Terminal Type |
|-------------|--------------------------------|---------------|
| EC35        | SPDT, 5 Pin Slim Line (Fig. 1) | PC Board      |
| EC50        | DPDT, 8 Pin Slim Line (Fig. 2) | PC Board      |

ELECTRICAL RATINGS: • 300 Volts, 12 Amps








## ACCESSORY

MH12-2 ..... Hold Down Spring  
MH16-2 ..... Hold Down Spring  
MH25-2 ..... Hold Down Spring




CUSTOM CONNECTOR CORPORATION





# Automotive Relay Sockets




| Mfr.'s Type   | Description                                                  | Terminal Type |
|---------------|--------------------------------------------------------------|---------------|
| BR04-PCB-0    | 4 Pin (Fig. 1)                                               | PC Board      |
| BR04-PCB-T    | 4 Pin (Fig. 2)                                               | PC Board      |
| BR05-PCB      | 5 Pin (Fig. 3)                                               | PC Board      |
| BR05-PCB-1P   | 5 Pin Without Locator Pins (Fig. 3)                          | PC Board      |
| BR05-SPCB     | 5 Pin (Fig. 3)                                               | PC Board      |
| BR05-SPCB-1P  | 5 Pin Without Locator Pins (Fig. 3)                          | PC Board      |
| BR05-FW 5 Pin | 5 Pin Connector for Wire Harnessing (Fig. 4)                 | Crimp         |
| BR05-WH 5 Pin | 5 Pin Connector for Wire Harnessing (Fig. 5)                 | Crimp         |
| BR05-WHF      | 5 Pin Relay or Flasher Connector for Wire Harnessing (Fig.6) | Crimp         |




| Mfr.'s Type | Description                                    | Terminal Type |
|-------------|------------------------------------------------|---------------|
| PR04-WH     | 4 Pin Automotive Connector for Wire Harnessing | Crimp         |



| Mfr.'s Type | Description                     | Terminal Type |
|-------------|---------------------------------|---------------|
| VR04-PCB-0  | 4 Pin Automotive (Fig. 1)       | PC Board      |
| VR05-PCB    | 5 Pin Micro Automotive (Fig. 2) | PC Board      |
| VR05-LFW    | 5 Pin Micro Automotive (Fig. 3) | Crimp         |
| VR05-FW     | 5 Pin Micro Automotive (Fig. 4) | Crimp         |



## ELECTRONIC PACKAGING PRODUCTS, HEADERS AND ENCLOSURES



| Mfr.'s Type      | Description                    | Dimensions              |
|------------------|--------------------------------|-------------------------|
| FB08             | 8 Pin Octal Style Male Header  | 1.375" X 1.375"         |
| FB11             | 11 Pin Octal Style Male Header | 1.375" X 1.375"         |
| FCBP, FCCP, FCWP | Enclosures                     | 1.375" x 1.375" x 1.925 |
| HB08             | 8 Pin Octal Style Male Header  | 2.375" x 1.75"          |
| HB11             | 11 Pin Octal Style Male Header | 2.375" x 1.75"          |
| HCBP, HCCP, HCWP | Enclosures                     | 2.375" x 1.75" x 2.625" |
| JCBP, JCCP, JCWP | Enclosures                     | 2.375" x 1.75" x 3.313" |
| DCBP, DCCP, DCWP | Enclosures                     | 2.375" x 1.75" x 2.750" |
| HMS-1            | Header Mounting Screw          | Header Mounting Screw   |

| Mfr.'s Type | Description                      | Dimensions              |
|-------------|----------------------------------|-------------------------|
| E1BV2020    | Enclosure                        | 2.022" X 2.022" X .750" |
| E1BV2020H   | Enclosure w/ molded in heat sinc | 2.022" X 2.022" X .750" |
| E1BV2525    | Enclosure                        | 2.513" x 2.513" x .750" |
| C1BV2020    | Cover for E1BV2020               | 2.022" x 2.022"         |
| E2BV2720    | Enclosure                        | 2.00" x 2.700" x .825"  |
| E2BV4530    | Enclosure                        | 3.00" x 4.500" x .825"  |



CUSTOM CONNECTOR CORPORATION



# Relay Sockets

•ULrecognized, File No. E60008  
•CSAcertified, File No. LR29513




Fig. 1






Fig. 2




| Mfr.'s Type | Description                 | Terminal Type         |
|-------------|-----------------------------|-----------------------|
| OT08        | DPDT, 8 Pin Octal (Fig. 1)  | Binder Head Screws    |
| OT08-PC     | DPDT, 8 Pin Octal (Fig. 1)  | Pressure Clamp Screws |
| OT11        | 3PDT, 11 Pin Octal (Fig. 2) | Binder Head Screws    |
| OT11-PC     | 3PDT, 11 Pin Octal (Fig. 2) | Pressure Clamp Screws |

Electrical Rating: • OT08 - 600 Volts, 10 Amps  
• All others - 300 Volts, 10 Amps




| Mfr.'s Type | Description        | Terminal Type         |
|-------------|--------------------|-----------------------|
| ST08        | DPDT, 8 Pin Blade  | Binder Head Screws    |
| ST08-PC     | DPDT, 8 Pin Blade  | Pressure Clamp Screws |
| ST11        | 3PDT, 11 Pin Blade | Binder Head Screws    |
| ST11-PC     | 3PDT, 11 Pin Blade | Pressure Clamp Screws |

Electrical Rating: • 300 Volts, 15 Amps




ACCESSORY

HDB-8 ..... Hold Down Spring



| Mfr.'s Type | Description            | Terminal Type         |
|-------------|------------------------|-----------------------|
| MT08-PC     | DPDT, 8 Pin Miniature  | Pressure Clamp Screws |
| MT14-PC     | 4PDT, 14 Pin Miniature | Pressure Clamp Screws |

Electrical Rating: • 300 Volts, 7 Amps




ACCESSORY

HDB-4 ..... Hold Down Spring



| Mfr.'s Type | Description        | Terminal Type         |
|-------------|--------------------|-----------------------|
| GT08-PC     | DPDT, 8 Pin Midget | Pressure Clamp Screws |


Electrical Rating: • 300 Volts, 10 Amps  
• 150 Volts, 15 Amps




ACCESSORY

HDB-4 ..... Hold Down Spring


C-103-PM prepunched aluminum  
DIN rail (1 meter lengths)



C-104-PM prepunched steel  
DIN rail (1 meter lengths)



C-105-PM prepunched steel  
DIN rail (1 meter lengths)



C-106-2PM prepunched steel  
DIN rail (2 meter lengths)

