




受控 CONTROLLED DOCUMENT					
编号 P/N	32- 5958UL	版本 Rev	0B	日期 Rel'd Date	Mar 24,08

DRAWING NO. 32-5958UL					
REVISIONS					
RELEASE FOR QUOTATION					
A	08-31-05	Y	W	T	
ADDED: NOTE 4 & 5, CONTACT					
B	10-26-05	Y	W	T	



NOTES:

1. ELECTRICAL SPECIFICATIONS

INSULATION RESISTANCE: 1000 MEGOHMS
WITHSTAND VOLTAGE: 1000V,AC/ MINUTE

2. MECHANICAL SPECIFICATIONS



CONTACT MATERIAL: PHOSPHOR BRONZE 0.3MM THICKNESS
CONTACT PLATING: 50 MICRO-INCH GOLD PLATE OVER 100
MICRO-INCH NICKEL PLATING
HOUSING MATERIAL: POLYCARBONATE
DURABILITY: 1000 CYCLES MIN
UL FLAMABLY RATING: 94-V0

3. ENVIRONMENTAL SPECIFICATIONS


TEMPERATURE RANGE: -40 °C TO +70 °C

4. FOR FLAT OVAL OR ROUND CABLE

5. FOR SOLID OR STRANDED WIRE APPLICATIONS



CONTACT



TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY BETTY.YU	DATE 10-26-05
DECIMALS	mm	CHECKED BY IVON.W	DATE 10-26-05
X	± 0.5	APPROVED BY THOMAS	DATE 10-26-05
X.X	± 0.15		
X.XX	± 0.10		
ANGLES	± 0.5°	U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER,
DO NOT SCALE DRAWING OR UPDATE MANUALLY.

SHEET 1 OF 1		DRAWING NO. 32-5958UL	SIZE C
-----------------	--	--------------------------	-----------

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1994

COMPANY CONFIDENTIAL



Connectivity
Solutions

TITLE
RJ45 MOD PLUG 50"U,STR,FLAT