


A fully screened robust range of DIN connectors for use in instrumentation and audio applications. Available in two finishes; bright nickel and non-reflective electrically conductive matt black. Robust construction incorporating cable grip and strain relief.

Manufactured to DIN 41524, 45322, 45326, 45327 and 45329.

- MATERIALS
- HOUSING : Zinc Alloy
heavy nickel plated
over copper
- MOULDING : Nylon
- CONTACTS : Brass
Silver Plated
- CABLE CLAMP : Mild Steel
zinc plated
- GROMMET : Black P.V.C.

- ELECTRICAL RATINGS
- Working Voltage 100 Vd.c. or a.c. peak
- Test Voltage 1000 Vd.c.
- Insulation Resist. $10^{11} \Omega$ min at 100 Vd.c.
- Current Rating 4 A
- Contact Resist. 10 m Ω max
- Capacity (mated) 3 pF
- Temp. Range -25°C to +70°C

Dimensions



Type	Deltron No
3 Way	590-0300
4 Way	590-0400
4 Way Switched	590-0410
5 Way 45°	590-0500
5 Way 60°	590-0510
5 Way Dice	590-0520
6 Way	590-0600
7 Way	590-0700
8 Way	590-0800

CONVERTED FROM PS0458 ISS4 (08.07.96) IN JAN 2003