

T18R6-7K2

Standard Cable Tie, 4" Long, 18lb Tensile Strength, PA66, Blue/Violet Striped, 50/bag

Article Number: 111-01780

Part Number: T18R6-7K2

Type: T18R

→ Find a Distributor

➔ Order Samples

➔Get Technical Drawings



 Base Data

Part No.	T18R6-7K2
Type	T18R
Color	Purple (PE) / Blue (BU)
Features	• Inside serrations allow for strong hold on cables and wire bundles. • Head design provides high tensile strength with very low insertion force. • Bent tail ensures a quick and simple installation.
Application Method	Quick, simple fixing by hand or with HellermannTyton tensioning tools
Identification Plate Position	none
Releasable Closure (Yes/No)	No
Typical Application	Used to bundle and secure wire and cable.
Variant	Inside Serrated

➔ Product Dimensions

Min. Tensile Strength	18.0lbs / 80.0N
Length (L)	4.0" / 100.0mm
Width (W) (imperial)	0.1"
Width (W)	2.45mm
Min. Ø Bundle	0.06" / 1.5mm
Max. Ø Bundle	0.86" / 22.0mm

➔ Material and Specifications

Material	Polyamide 6.6 (PA66)
Flammability	UL94 V2
Material Specification	RoHS / HF
Operating Temperature	-40 °F to +185 °F (-40 °C to +85 °C)
ROHS Conformity	
Specification	MIL 53421 / UL ZODZ2.E64139
UL Listed (US and Canada)	No
UL Recognized (US and Canada)	No

➡ **Logistic and Packaging**

Packaging Type	bag
Pkg. Qty.	50
Carton Qty.	10000
EAN code	4031026433639
UPC	089306070016

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

[Home](#) | [About HellermannTyton](#) | [Products](#) | [Careers](#) | [Contact](#) | [Terms](#)

© HellermannTyton North America 2011 | [TS16949](#), [ISO 9001](#) and [ISO 14001 Certified](#)

7930 N. Faulkner Rd. Milwaukee, WI 53224-9517 | Fax: 800-848-9866 | Phone: 800-537-1512