

64210

OSRAM ORIGINAL LINE | Halogen headlight lamps for cars



Areas of application

- Headlight

Product benefits

- OEM Quality
- Wide product range
- Reliable quality

Product features

- Original spare parts

Technical data

Electrical data



Power input	58 W ¹⁾
Nominal wattage	55 W
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Light technical data

Color temperature	3200 K
Luminous flux	1500 lm
Luminous flux tolerance	±10 %

Dimensions & weight



Product line drawing

Base

Length	59.0 mm
Diameter	11.0 mm
Product weight	12.50 g

Lifespan

Lifespan B3	330 h
Lifespan Tc	550 h

Additional product data

Base (standard designation)	PX26d
-----------------------------	-------

Product datasheet

Certificates & standards

ECE category	H7
--------------	----

Country specific categorizations

Order reference	64210
-----------------	-------

Country specific information

Product code	METEL code	SEG number	STK number	UK Org
4050300332185	OSRA64210	8328066	4739957	-
4050300925202	OSRA64210BLI1	8328414	4730311	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4050300332185	64210	Folding carton box 1	34 mm x 34 mm x 58 mm	0.07 dm ³	42.40 g
4050300332192	64210	Bundle 10	173 mm x 58 mm x 68 mm	0.68 dm ³	185.60 g
4050300332208	64210	Shipping carton box 100	186 mm x 129 mm x 356 mm	8.54 dm ³	1727.00 g
4050300925202	64210	Blister 1	73 mm x 41 mm x 119 mm	0.36 dm ³	23.67 g
4008321141613	64210	Shipping carton box 10	117 mm x 145 mm x 279 mm	4.73 dm ³	328.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.