


1.	MODEL:	40RE08-1
2.	Dimension	Outer Diameter 40 mm. Baffle Opening 36.5 mm.
		Height Refer to Drawing . Weight 27.2 Grams.
3.	Magnet	Materials Rare Earth . Size Ø 19 X 3.4 mm.
4.	Nominal Impedance	8 Ω $\pm$ 15 % At 850 Hz.
5.	Power Rating	Normal 3 W. Maximum 4 W.
6.	Lowest Resonant Frequency	190 $\pm$ 20 % Hz.
7.	Output Sound Pressure Lever (S.P.L.)	85 $\pm$ 3 db / 1Watt . 0.5 Meter.
		Average at 600, 800, 1000, 1200 Hz.
8.	Frequency Range	100 ~ 20000 Hz. Average S P L - 10 db.
9.	Distortion	5 % Maximum At 1000 Hz. 1 W.
10.	Abnormal Sound Test	Must Be Normal Test By 4.9 Volts. Sine Wave.
11.	Load Test	White Noise With Weighted Filter 4.9 Volts.(RMS) 96 Hrs.
12.	Polarity	Diaphragm shall move Forward when Apply a Positive DC.
		Current to the "+" or "Marked" Terminal.


MOUNTING NOTICE



Unit : mm

Housing Material : ABS

P40RE08-1 VOL:2.83V(1W) DIS:0.5M VANSONIC
X:1.0000kHz *Y:84.80dB ZA:1.0000 SSR Fund.



20-SEP-2004 11:04:36

Mode: SSR