



 Deutsche Version

[Home](#)

[About Us](#)

[Products](#)

[Audio](#)

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

☐ PRODUCTS
ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NEUTRIK



Audio

DIN Connectors

[back](#)

NYS321G

Product

Connector Type	DIN
Gender	male

Electrical

Contact resistance	< 10 mΩ
Dielectric strength	0,5 kVdc
Rated current per contact	depends on mated connector A

Mechanical

Cable O.D.	≤ 5 mm
Wire size	26 AWG

Material

Bushing	PVC
Contact plating	0.2 µm Au
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA 6 30 % GR)
Shell	Zinc diecast (ZnAl4Cu1), gal Ni plated
Strain relief	CRIMP type zn plated

Environmental

Solderability	Complies with IEC 68-2-20
Temperature range	-20 °C to +70 °C