



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	N	REV PER ECR 10-000722	25JAN10	JR	TM
	N1	REVISED PER ECO-17-004099	23AUG2017	RS	DR



AMP WIRE RANGE	E13288 Listed	LR7189 Certified
2/0 AWG SOLID OR STRANDED	2/0 AWG STRANDED	2/0 AWG SOLID OR STRANDED

- 1

STAMP AMP 2/0W* APPROX AS SHOWN.
- 2

COPPER PER ASTM B-152, ANNEALED.
- 3

TIN PLATE 0.00254 [.000100] MIN THK
EXT. PER ASTM B-545.
- 4 MAX RECOMMENDED OPERATING TEMP
IS 170°C.
- 5 WIRE CROSS SECTIONAL AREA RANGE:
60.6-76.3mm [119,500-150,500] CMA
SOLID OR STRANDED.

50	LOOSE PIECE	36923
QTY	PACKAGING TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DK. SCHRUM 1/14/94	TE Connectivity			
		CHK AJ KAUFMAN 1/19/94				
		APVD JL MECKLEY 1/19/94				
		PRODUCT SPEC				
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	—	NAME			
	0 PLC ± - 1 PLC ± - 2 PLC ± 0.20 [.008] 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APPLICATION SPEC	TERMINAL, RING TONGUE, SOLISTRAND			
MATERIAL	2	—	SIZE A2	CAGE CODE 00779	DRAWING NO C=36923	RESTRICTED TO —
CUSTOMER DRAWING			SCALE 2:1	SHEET 1 of 1	REV N1	