


# PIN RECEPTACLES

FOR .032" - .046" DIAMETER PINS

## 0344

0344-X-19-XX-34-XX-10-0

Swage mount in .067 hole




| Basic Part Number | Board Thickness | Length V | Depth D |
|-------------------|-----------------|----------|---------|
| 0344-1            | .031            | .062     | .040    |
| 0344-2            | .062            | .094     | .062    |
| 0344-3            | .094            | .125     | .062    |
| 0344-4            | .125            | .156     | .062    |

## 0349

0349-X-31-XX-34-XX-10-0

Swage mount in .129 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 0349-2            | .062            | .094     |
| 0349-3            | .094            | .125     |
| 0349-4            | .125            | .156     |

## 0323

0323-X-15-XX-34-XX-10-0


Swage mount in .094 hole



## 0324

0324-X-15-XX-34-XX-10-0

Swage mount in .094 hole




| Basic Part Number | Board Thickness | Length V |
|-------------------|-----------------|----------|
| 032X-1            | .031            | .062     |
| 032X-2            | .062            | .094     |
| 032X-3            | .094            | .125     |
| 032X-4            | .125            | .156     |
| 032X-5            | .188            | .219     |

## 0348

0348-0-33-XX-34-XX-10-0


Wire crimp termination. Accepts wire sizes 20 AWG Max. / 24 AWG Min.



## 0405

0405-0-15-XX-34-XX-04-0


Press-fit in .084 mounting hole



## 0336

0336-0-15-XX-34-XX-04-0


Press-fit in .089 mounting hole



## 0322

0322-0-15-XX-34-XX-10-0


Solder mount in .089 min. mounting hole



## 0325

0325-0-15-XX-34-XX-10-0

Press-fit in .090 mounting hole



### SPECIFICATIONS:

Shell Material: Brass Alloy 360, 1/2 Hard

Contact Material: Beryllium Copper Alloy 172, HT

Dimensions: Inches

Tolerances On: Lengths:  $\pm .005$

Diameters:  $\pm .002$

Angles:  $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - 34 - XX - XX - 0

BASIC PART #

SPECIFY SHELL FINISH:

01 200  $\mu$ " TIN/LEAD OVER NICKEL

◆ 80 200  $\mu$ " TIN OVER NICKEL (RoHS)

◆ 15 10  $\mu$ " GOLD OVER NICKEL (RoHS)

SPECIFY CONTACT FINISH:

01 200  $\mu$ " TIN/LEAD OVER NICKEL

◆ 80 200  $\mu$ " TIN OVER NICKEL (RoHS)

◆ 27 30  $\mu$ " GOLD OVER NICKEL (RoHS)

SELECT CONTACT:

#34 CONTACT (DATA ON PAGE 258)

(For alternate contact choices, see group E on page 248)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Mill-Max:

[0405-0-15-80-34-27-04-0](#) [0344-2-19-15-34-27-10-0](#) [0322-0-15-15-34-27-10-0](#) [0405-0-15-01-34-01-04-0](#) [0322-0-15-01-34-27-10-0](#) [0344-2-19-01-34-27-10-0](#) [0405-0-15-01-34-27-04-0](#) [0349-4-31-01-34-01-10-0](#) [0349-4-31-01-34-27-10-0](#) [0349-3-31-01-34-01-10-0](#) [0349-3-31-01-34-27-10-0](#) [0349-2-31-01-34-01-10-0](#) [0349-2-31-01-34-27-10-0](#) [0348-0-33-01-34-01-10-0](#) [0344-4-19-01-34-01-10-0](#) [0344-4-19-01-34-27-10-0](#) [0344-3-19-01-34-01-10-0](#) [0344-3-19-01-34-27-10-0](#) [0344-2-19-01-34-01-10-0](#) [0344-1-19-01-34-01-10-0](#) [0344-1-19-01-34-27-10-0](#) [0336-0-15-01-34-01-04-0](#) [0336-0-15-01-34-27-04-0](#) [0325-0-15-01-34-01-10-0](#) [0325-0-15-01-34-27-10-0](#) [0324-5-15-01-34-01-10-0](#) [0324-5-15-01-34-27-10-0](#) [0324-4-15-01-34-01-10-0](#) [0324-4-15-01-34-27-10-0](#) [0324-3-15-01-34-01-10-0](#) [0324-3-15-01-34-27-10-0](#) [0324-2-15-01-34-01-10-0](#) [0324-2-15-01-34-27-10-0](#) [0324-1-15-01-34-01-10-0](#) [0324-1-15-01-34-27-10-0](#) [0323-5-15-01-34-01-10-0](#) [0323-5-15-01-34-27-10-0](#) [0323-4-15-01-34-01-10-0](#) [0323-4-15-01-34-27-10-0](#) [0323-3-15-01-34-01-10-0](#) [0323-3-15-01-34-27-10-0](#) [0323-2-15-01-34-01-10-0](#) [0323-2-15-01-34-27-10-0](#) [0323-1-15-01-34-01-10-0](#) [0323-1-15-01-34-27-10-0](#) [0322-0-15-01-34-01-10-0](#) [0323-1-15-15-34-27-10-0](#) [0323-2-15-15-34-27-10-0](#) [0323-3-15-15-34-27-10-0](#) [0323-4-15-15-34-27-10-0](#) [0323-5-15-15-34-27-10-0](#) [0324-1-15-15-34-27-10-0](#) [0324-3-15-15-34-27-10-0](#) [0324-4-15-15-34-27-10-0](#) [0324-5-15-15-34-27-10-0](#) [0325-0-15-15-34-27-10-0](#) [0344-1-19-15-34-27-10-0](#) [0344-3-19-15-34-27-10-0](#) [0344-4-19-15-34-27-10-0](#) [0349-2-31-15-34-27-10-0](#) [0349-3-31-15-34-27-10-0](#) [0349-4-31-15-34-27-10-0](#) [0405-0-15-15-34-27-04-0](#) [0323-3-15-00-00-00-10-0](#) [0323-1-15-00-00-00-10-0](#) [0323-2-15-00-00-00-10-0](#) [0325-0-15-00-00-00-10-0](#) [0324-4-15-00-00-00-10-0](#) [0344-4-19-00-00-00-10-0](#) [0324-1-15-00-00-00-10-0](#) [0324-5-15-00-00-00-10-0](#) [0324-2-15-00-00-00-10-0](#) [0323-4-15-00-00-00-10-0](#) [0349-2-31-00-00-00-10-0](#) [0348-0-33-00-00-00-10-0](#) [0322-0-15-00-00-00-10-0](#) [0323-5-15-00-00-00-10-0](#) [0349-3-31-00-00-00-10-0](#) [0344-2-19-00-00-00-10-0](#) [0349-4-31-00-00-00-10-0](#) [0405-0-15-00-00-00-04-0](#) [0344-1-19-00-00-00-10-0](#) [0344-3-19-00-00-00-10-0](#) [0324-3-15-00-00-00-10-0](#) [0349-3-31-01-34-14-10-0](#) [0349-2-31-01-34-14-10-0](#) [0344-4-19-01-34-14-10-0](#) [0348-0-33-80-34-14-10-0](#) [0323-4-15-01-34-14-10-0](#) [0325-0-15-01-34-14-10-0](#) [0323-2-15-80-34-14-10-0](#) [0324-4-15-80-34-14-10-0](#) [0323-3-15-80-34-14-10-0](#) [0324-2-15-01-34-14-10-0](#) [0322-0-15-01-34-14-10-0](#) [0324-5-15-01-34-14-10-0](#) [0324-2-15-80-34-14-10-0](#) [0323-2-15-01-34-14-10-0](#) [0336-0-15-80-34-14-04-0](#) [0324-4-15-01-34-14-10-0](#)