


# PA SPEAKERS

## 5 WAY STEREO SPEAKER SELECTOR

This professional quality selector box is designed to help distribute quality sound throughout your complete Home Theater System. There is built-in protection for your amplifier. The switch can control up to five (5) stereo pairs of speakers in any combination and maintains a constant impedance load to the amplifier.



No. 44-505



### Specifications:

Power: 50 Watts RMS per Channel  
Max Power: 75 Watts per Channel  
Load Protection: Non Inductive 50 Watts  
Outputs: 5 Stereo Speaker Pairs  
+ 1 1/4" Headphone Jack  
Size: 8" W x 4" D x 2" H  
Case: Black Metal

## 6" ALUMINUM PA SPEAKER WEATHER PROOF

No. WP10



- HORN MATERIAL - Aluminum - Baked Gray Enamel Finish
  - Weather proof sealed
  - Heavy duty metal mounting bracket
  - Rubber edge guard on metal horn
- FREQUENCY RESPONSE 250-15,000 Hz.
- POWER RATING 15 Watts Maximum
- SENSITIVITY 105 dB / 1W / 1M
- VOICE COIL IMPEDANCE 8 ohm
- SIZE 6" Diameter  
6" Length

## REFLEX TRUMPET 5-1/4" INDOOR / OUTDOOR

A compact speaker for all purposes

No. WP4



### UNIVERSALLY DESIGNED FOR:

- BOATING PAGING HORN
- FIXED OR MOBILE COMMUNICATIONS
- SECURITY

MODERATELY PRICED - IDEAL WHERE WIDE FREQUENCY RESPONSE IS NOT A FACTOR

### ALL EXPOSED METAL STAINLESS STEEL

This highly efficient speaker is a true re-entrant horn design. The speaker is totally weatherproof and has a white plastic casing of high impact, rugged construction. Can be mounted anywhere, with the 110° adjustable swivel bracket and screw flange.

Supplied with 12 ft. length weatherproof leads with 3.5mm phone plug on lead.

### SPECIFICATIONS:

Power Handling Nominal Capacity: 8 watts (Handles up to 15 watts)  
Frequency Response: 700 to 7000Hz  
Impedance: 8 ohms  
Overall size: 5-1/4" dia. x 6" depth

## HORN 30 WATT 8" OUTDOOR

No. WP20

- HAILING
- PA
- PAGING



- WATERPROOF
- RUST/SHOCK RESISTANT
- STAINLESS STEEL MOUNTING HARDWARE
- COMPLETELY SEALED FOR MARINE & MOBILE APPLICATIONS

A smooth, wide frequency response of 450-10,000Hz assures excellent dispersion of music and voice. 30W of continuous power (60W peak) makes it capable of reproducing clear and crisp sound over long distances in noisy terrain. A rubber sealing gasket is provided for sealing mounting base to wall.

Its sleek white lines make this rugged plastic horn ideally suitable for marine craft of all sizes.

### SPECIFICATIONS:

Input power: 30W continuous, 60W peak  
Impedance: 8 ohms  
Freq. Resp.: 450-10K Hz.  
Magnet: 10 oz. ferrite  
Size: 8" x 4-1/2" x 9-1/4" long