

Search Results

Evaluate  
- FAQ's  
Design a Solution  
- Part Drawings  
- PDF-QuickNet HDQ ..  
- Specification Sheets  
- PDF-QuickNet Cas ..  
- PDF-QuickNet HDQ ..

How to Buy  
- Bill of Material  
- Favorite Products List  
- Locate Distributor  
Install & Maintain  
- Installation Instructions  
- PDF-Installation ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

**Text Search: 'F1RBXO-9608-10S'**

Your search criteria matched only one product, shown below

**F1RBXO-9608-10S**



Quicknet™ HDQ Series High Density Fiber Optic Cassettes:

- Mounts to standard 19" rack rails
- Low insertion loss of 0.5dB max, per optimized cassette and 0.75dB max. per standard cassette; ensures system meets IEEE 802.3ae max. channel loss specification of < 2.6dB
- Return loss: ≥ 26dB
- Adapter housing colors follow TIA/EIA - 568-C.3 suggested color identification scheme
- Connect together with high-density female MTP\* cable assemblies as interconnection network
- Significantly reduce installation time and labor by eliminating field connector termination
- Factory terminated, assembled, and 100% tested
- Insertion loss data provided on every fiber cassette
- Lifetime traceability of test data to a Q.C. number
- 10Gig OM3 50/125um fiber cassettes are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10 Gb/s for link lengths up to 300 meters and up to 550 meters for OM4 at 850 nm; backward compatible with all 50/125um (OM2) MPO or MTP system

requirements

Quicknet™ Cassette Rear Cable Manager:

- Mounts horizontally to standard 19" rack rails
- Fiber Management Slack Spools can be used to manage MTP Interconnect Cable

|                                |   |
|--------------------------------|---|
| • Part Number                  | F1RBXO-9608-10S   |
| • RoHS Compliancy Status       | Compliant   |
| • Part Description             | QuickNet™ HDQ Series High Density Fiber Optic Cassette; 1RU 96-fiber B-type labeling; 10Gb Optimized OM3 8-fiber MTP to LC Pre-terminated- standard polarity. |
| • Pricing Description          | 8 Fiber High Density OM3 10GbE MTP To LC Cassette Optimized - B-type labeling   |
| • Min. Order UOM               | PC  |
| • Min. Order Qty.              | 1   |
| • BOM Qty. (# of Pkgs.)        | <input type="text" value="0"/>  |
| • Add to Favorite Product List | <input type="checkbox"/>  |

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.