

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

130106-0098

Status:

Active

Overview:

Stringlights

Description:

Super-Safeway™ Molded Rubber Stringlight 200W 12/2 SOOW 1.52m (5.0') Lead 10 Sockets, Overall Length 30.48m (100.0')



Documents:

RoHS Certificate of Compliance (PDF)

General	
Product Family	Portable Lighting
Series	130106
NEMA Configuration	NEMA 1-15
NEMA Rating	Rain Tight
Outlet	None
Overview	Stringlights
Product Name	Super-Safeway™
Type	String Lights
UPC	78678879860
Woodhead	Yes
Physical	
Cord Length - Primary	1.52m (5.0')
Cord Length - Secondary	1.52m (5.0')
Depth	47.625mm (1.875")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	107.95mm (4.250")
Length	30.48m (100.0')
Material - Guard	N/A
Mounting Style	Stringer
Packaging Type	Carton
Socket Construction	Rubber Molded
Electrical	
Bulb Type	Incandescent
Cord Type - Primary	12/2 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	200W
Lumens	2000
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Old Part Number	320122

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

130106Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION