




Wiha Combination Wrenches



400 Combination Wrenches Inch DIN 3113A/ISO 3318 - ISO 7738

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit.

Item No.	AF	OAL	OAL	H ¹	H ²	D ¹	D ²	lbs.	pkg.
	Inch	mm	Inch	mm	mm	mm	mm		
400 43	1/4	100	3.9	5.0	3.9	10.1	15.7	.03	10
400 44	5/16	120	4.7	5.9	4.4	12.9	19.0	.05	10
400 45	3/8	140	5.5	6.9	5.0	15.9	22.8	.09	10
400 46	7/16	150	5.9	7.4	5.2	17.3	25.4	.11	10
400 47	1/2	170	6.7	8.4	5.8	20.2	29.3	.14	10
400 48	9/16	180	7.1	8.9	6.1	21.6	31.2	.19	10
400 49	19/32	190	7.5	9.3	6.3	23.1	33.0	.21	10
400 50	5/8	200	7.8	9.8	6.6	24.6	34.5	.23	10
400 51	11/16	210	8.2	10.3	6.9	25.9	37.3	.30	10
400 52	3/4	230	9.0	11.1	7.3	28.8	40.4	.34	1
400 53	25/32	240	9.4	11.4	7.5	30.2	42.3	.39	1
400 54	13/16	250	9.8	11.7	7.7	31.7	44.2	.45	1
400 55	7/8	260	10.2	12.0	7.9	33.0	46.6	.51	1
400 56	15/16	280	11.0	12.7	8.3	35.8	50.1	.63	1
400 57	1	290	11.4	13.0	8.5	37.3	52.8	.65	1
400 58	1-1/16	310	12.2	13.6	8.9	40.2	55.9	.83	1
400 59	1-1/8	330	13.0	14.2	9.3	42.8	59.8	.98	1
400 60	1-1/4	360	14.1	15.2	9.9	47.2	66.9	1.31	1
400 61	1-5/16	360	14.1	15.2	9.9	47.2	66.9	1.28	1
400 62	1-3/8	400	15.7	22.8	14.1	54.6	77.5	2.56	1
400 63	1-7/16	400	15.7	22.8	14.1	54.6	77.5	2.38	1
400 64	1-1/2	400	15.7	22.8	14.1	54.6	77.5	2.33	1
400 65	1-5/8	450	17.6	25.8	15.8	62.1	83.7	3.19	1
400 66	1-3/4	500	19.6	28.8	17.5	69.6	93.1	4.44	1
400 67	1-13/16	500	19.6	28.8	17.5	69.6	93.1	4.31	1
400 68	2	540	21.2	31.2	18.9	75.6	102.6	5.72	1

400 89 Set 15 Piece Inch Combination Wrenches Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit. In roll up pouch

Item				OAL		
No.		Inch	mm		Inch	mm
400 89	400 43	1/4	100	400 52	3/4	230
	400 44	5/16	120	400 54	13/16	250
	400 45	3/8	140	400 55	7/8	260
	400 46	7/16	150	400 56	15/16	280
lbs.	400 47	1/2	170	400 57	1	290
6.21	400 48	9/16	180	400 58	1-1/16	310
	400 50	5/8	200	400 59	1-1/8	330
	400 51	11/16	210			



400 91 Set 12 Piece Inch Combination Wrenches

Made from 31CRV3 high performance tool steel. Satin chromed sure grip body. Precision formed for exact fit. In roll up pouch

Item				OAL		
No.		Inch	mm			OAL
					Inch	mm
400 91	400 44	5/16	120	400 51	11/16	210
	400 45	3/8	140	400 52	3/4	230
lbs.	400 46	7/16	150	400 54	13/16	250
7.50	400 47	1/2	170	400 55	7/8	260
	400 48	9/16	180	400 56	15/16	280
	400 50	5/8	200	400 57	1	290