






NOTES

- A: MODEL NAME, INPUT VOLTAGE RANGE, NOMINAL OUTPUT VOLTAGE,
MAXIMUM OUTPUT CURRENT, COUNTRY OF MANUFACTURE AND
MARKING ARE SHOWN HERE IN ACCORDANCE WITH THE SPECIFICATIONS.
- B: INPUT AND OUTPUT TERMINALS : 4- $\phi 1 \pm 0.1$
- C: UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCE : ± 0.3



*TERMINAL ASSIGNMENTS

- ①.....AC(N) INPUT
②.....AC(L) INPUT
③.....-V OUTPUT
④.....+V OUTPUT

*MATERIAL

CASE : PLASTIC(UL94V-0)
PBT t:1.0mm

(unit : mm)

MODEL NAME	KWS25A
TDK-Lambda	
FC005-02-01	