




MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
1201140084	BTY803P-FBC	-

VOLTAGE RATING	10-30 VDC
AMPERAGE RATING PER PORT	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-20°C TO 90°C
UL CERTIFICATIONS	UL RECOGNIZED, FILE NO. E46237
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
2	O-RING	VITON	RED
3	RECEPTACLE SHELL	BRASS	NICKEL PLATED
4	HOUSING	PBT	YELLOW
5	LABEL	ABS	WHITE
6	LENS	NYLON	CLEAR



NOTE
FACE VIEW
ON CONNECTOR

DESCRIPTION EC NO: WU2010-0445 DRWN: LSTEMMLE 2010/03/19 CHKD: NSTAUDIG APPR: NSTAUDIG 2010/03/23	DESCRIPTION	QUALITY SYMBOLS ▽ = 0 ◁ = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE MM ONLY		SCALE 2:1	DESIGN UNITS METRIC	 FIRST ANGLE PROJECTION	
				mm	INCH	DRAWN BY LSTEMMLE	DATE 2010/03/19	MICRO-CHANGE MPIS 8 PORT PNP TWIN PORT 5P 19 PO. HARDSHELL CONN.			
			4 PLACES	±---	±---	CHECKED BY	DATE				
			3 PLACES	±---	±---	FP	2010/03/22				
			2 PLACES	±---	±.01	APPROVED BY	DATE		MOLEX INCORPORATED		
			1 PLACE	±0.3	±---	NSTAUDIG	2010/03/22				
			ANGULAR ± --- °			MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SEE TABLE		SD-120114-069				1 OF 1		
			SIZE A2	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							