



Search Results

- Evaluate
- FAQ's

- Line Cards

- PDF-Copper Cabli ..

- Performance Data

- PDF-ETL Channel ..

- PDF-ETL Short Ch ..

- Selection Guides

- PDF-TX6A 10Gig U ..
- Design a Solution
- Specification Sheets

- PDF-TX6A 10Gig U ..

- PDF-TX6A 10Gig U ..
- How to Buy
- Bill of Material

- Favorite Products List

- Locate Distributor
- Install & Maintain
- Installation Instructions

- PDF-Next Generat ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) Search Tips 

 Text Search: 'PUR6A04IG-UG'

Your search criteria matched only one product, shown below

PUR6A04IG-UG



- Exceeds requirements of ANSI/TIA-568-C.2 Category 6A, IEEE 802.3an-2006, and ISO 11801 Class E_A channel standards
- Exceeds requirements of ANSI/TIA-568-C.2 Category 6A and IEC 61156-5 Category 6_A component standards
- Meets requirements of IEEE 802.3af and IEEE 802.3at for PoE applications
- Patent-pending cable design suppresses alien crosstalk with enhanced internal electrical performance
- Round cable design with reduced cable diameter enables improved cable bundling and optimizes fill capacity
- Flame rating: UL1666
- Cable diameter: 0.295 in. (7.5mm) nominal, Plenum 0.310 (7.9mm) nominal
- Installation temperature range: 32°F to 140°F (0°C to 60°C)
- Operating temperature range: -4°F to 167°F (-20°C to 75°C)
- Descending length cable markings enable easy identification of remaining cable which

reduces installation time and cable scrap

▪ Part Number	PUR6A04IG-UG
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Category 6A, riser (CMR), 4-pair, UTP copper cable. Copper conductors are 23 AWG with flame-retardant PE insulation. Conductors are twisted in pairs, separated by an integrated pair divider, surrounded by a patent-pending matrix tape and protected by a flame-retardant PVC jacket.
▪ Product Type	Copper Cable
▪ Color	International Gray
▪ Cable Color	International Gray
▪ Cable Type	UTP
▪ CE Compliant	No
▪ Flammability Rating	CMR
▪ Jacket Material	Flame-retardant PVC
▪ Performance Level	Category 6A/Class EA
▪ Pricing Description	Copper Cable, Cat 6A, 4-Pair, 23 AWG, UTP, CMR, Intl Gray, 1000 Feet/305m
▪ Min. Order UOM	FT
▪ Min. Order Qty.	9000
▪ BOM Qty. (# of Pkgs.)	0
▪ Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.