


Section A-A

NOTES:

MATERIAL

- 1.Insulator Material:PBT+30%GF(UL94V-0)
2.Contact Material : Brass
3.Contact Plating :
AWP xx-8240-T : Gold flash over Ni
AWP xx-8540-T : Tin over Ni

ELECTRICAL

- 1.Current Rating : 3AMP
- 2.Voltage Rating : 500V AC/DC
- 3.Withstand Voltage : 1000V AC/DC
- 4.Contact Resistance : 20mΩ max
- 5.Insulation Resistance: 1000MΩ min

ENVIRONMENTAL

- 1.Operation Temperature: -40°C to +105°C
2.Packing: Tray

- ② 6P-8P Without Slot "M" and "N"
10P-12P With Slot "M", Without "N"
14P-64P With Slot "M" and "N"

G	RoHS compliant unit:mm	Scale	Free					Date	Name	Description: ③ DIN 41651 / IDC-socket 2.54mm pitch without central polarisation		G	
		TOLERANCE						Drawn	21.12.2009	Dean	ASSMANN WSW-NO. AWP xx-8x40-T		
		X.	±0.35					Approved	28.03.2013	Hellwig			
		.X	±0.25										
H		.XX	±0.20	③	Update Description	15.03.2022	Winnie					H	
		.XXX	±0.15	②	Drawn	28.03.2013	Dean				Drawing-No. ASS 2261A CO		rev03
		DIM	TOL	①	Drawn	21.12.2009	Dean				Customer-No.		SHEET 1 / 1
		Angle	TOL	Id.	modification	Date	Name						

	1	2	3	4	5	6	7	
--	---	---	---	---	---	---	---	--