

CAB CAB ABS 403018 T3B



Sample photo

Order symbol: CAB ABS 403018 T3B
Product nbr: 8183052
Description: Cabinet, ABS
Remarks: Locks on the long side

EAN:	6418074020314
El. number:	
Finland:	3424368
Denmark:	8212019056
Italy:	7812045
Sweden:	2540045
Norway:	

Including: Cabinet base, door with EPDM gasket, 3mm double bit lock(s) with key, screws for mounting plate/DIN-rail and corner plugs.

Dimensions:	Length	Width	Height
mm:	400	300	180
inch:	15.7	11.8	7.1

Materials:

Material:	ABS
Base colour:	RAL 7035
Cover colour:	Smoked grey
Gasket material:	EPDM

Temperatures:

Short term:	-40 ... 80 °C
Continuous:	-40 ... 60 °C
Short term:	-40 ... 175 °F
Continuous:	-40 ... 140 °F

Accessories:

EKIV 43	Mounting plate
EKIV 43 PL	Mounting plate, Plastic
EKIV 27	DIN-35 Mounting rail
DS3527OE1	DIN-35 Mounting rail
EKIV 37	DIN-35 Mounting rail
DS3537OE1	DIN-35 Mounting rail
FP A 43	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 43	Front plate
FP 12x2-43	Front plate
FP 12x3-43	Front plate
DRF 43/44	DIN rail frame set

Rating:

Ingress Protection (EN 60529): IP 65
Impact Resistance (EN 62262): IK 08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): Yes
Flammability Rating (UL 746 C 5): UL 94 HB
Glow Wire Test (IEC 695-2-1) °C: 650
NEMA Class: NEMA 1, 4, 4X, 12, 13

Certificates:

Fimko
Europe EN 62208: 2003
Gost R

