

STANDARD PLUGGABLE PRINTED CIRCUIT US Pin Spacing^a Headers

Horizontal or vertical headers offer different wire entry options and enhance plug accessibility. Closed end headers help prevent misplugging.

- Multipole, Single Mold Construction
- Industry Standard Compatible
- Horizontal and Vertical
- Open and Closed Ends
- Housing Material: Polyamide 6.6
- Standard Color: Green^b

^aBlocks with metric pin spacing begin on page 132.

Ratings

IEC/VDE

UL (File No. E101811)

CSA (File No. LR68503)

Ordering Information

Header, US (Inch) Pin Spacing

No. of
Poles

Type	Cat. No.	Length L mm (in.)	Std. Pk.	Current		Voltage	
				12A	15A	250V	300V
STLZ950/2-w	37.102	11.36 (.45)	100	12A	15A	250V	300V
STLZ950/3-w	37.103	16.44 (.65)	100				
STLZ950/4-w	37.104	21.52 (.85)	50				
STLZ950/5-w	37.105	26.60 (1.05)	50				
STLZ950/6-w	37.106	31.68 (1.25)	50				
STLZ950/7-w	37.107	36.76 (1.45)	30				
STLZ950/8-w	37.108	41.84 (1.65)	30				
STLZ950/9-w	37.109	46.92 (1.85)	30				
STLZ950/10-w	37.110	52.00 (2.05)	30				
STLZ950/11-w	37.111	57.08 (2.25)	20				
STLZ950/12-w	37.112	62.16 (2.45)	20				
STLZ950/13-w	37.113	67.24 (2.65)	20				
STLZ950/14-w	37.114	72.32 (2.85)	20				
STLZ950/15-w	37.115	77.40 (3.05)	20				
STLZ950/16-w	37.116	82.48 (3.25)	15				
STLZ950/17-w	37.117	87.56 (3.45)	15				
STLZ950/18-w	37.118	92.64 (3.65)	15				
STLZ950/19-w	37.119	97.72 (3.85)	15				
STLZ950/20-w	37.120	102.80 (4.05)	15				
STLZ950/21-w	37.121	107.88 (4.25)	10				
STLZ950/22-w	37.122	112.96 (4.45)	10				
STLZ950/23-w	37.123	118.04 (4.65)	10				
STLZ950/24-w	37.124	123.13 (4.85)	10				

Pin Spacing 5.08mm (.200)



Use with AKZ950, BU02, BU04, AKZ1200 Plugs

Type	Cat. No.	Length L mm (in.)	Std. Pk.	Current		Voltage	
				12A	15A	250V	300V
STLZ950/2-o	37.452	10.08 (.40)	100	12A	15A	250V	300V
STLZ950/3-o	37.453	15.16 (.60)	100				
STLZ950/4-o	37.454	20.24 (.80)	50				
STLZ950/5-o	37.455	25.32 (1.00)	50				
STLZ950/6-o	37.456	30.40 (1.20)	50				
STLZ950/7-o	37.457	35.48 (1.40)	30				
STLZ950/8-o	37.458	40.56 (1.60)	30				
STLZ950/9-o	37.459	45.64 (1.80)	30				
STLZ950/10-o	37.460	50.72 (2.00)	30				
STLZ950/11-o	37.461	55.80 (2.20)	20				
STLZ950/12-o	37.462	60.88 (2.40)	20				
STLZ950/13-o	37.463	65.96 (2.60)	20				
STLZ950/14-o	37.464	71.04 (2.80)	20				
STLZ950/15-o	37.465	76.12 (3.00)	20				
STLZ950/16-o	37.466	81.20 (3.20)	15				
STLZ950/17-o	37.467	86.28 (3.40)	15				
STLZ950/18-o	37.468	91.36 (3.60)	15				
STLZ950/19-o	37.469	96.44 (3.80)	15				
STLZ950/20-o	37.470	101.52 (4.00)	15				
STLZ950/21-o	37.471	106.60 (4.20)	10				
STLZ950/22-o	37.472	111.68 (4.40)	10				
STLZ950/23-o	37.473	116.76 (4.60)	10				
STLZ950/24-o	37.474	121.84 (4.80)	10				

Pin Spacing 5.08mm (.200)

Use with AKZ950, BU02, BU04, AKZ1200 Plugs

Dimensions			
mm	in.	mm	in.
1.00	0.039	8.20	0.323
2.00	0.079	8.40	0.331
3.10	0.122	11.30	0.445
3.50	0.138	12.00	0.472
3.80	0.150	15.16	0.597
3.90	0.154	15.26	0.601
5.08	0.200	16.44	0.647
7.90	0.311	17.00	0.669



^bGray available, please consult Altech