



[About Leviton](#)
[A Century of Success](#)
[Press](#)
[Join Our eMailing List](#)
[Trade Shows](#)
[RoHS](#)
[Career Opportunities](#)
[Contact Us](#)
[All Leviton Products](#)
[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)
[Library Home](#)
[Application Notes](#)
[Brochures / Catalogs](#)
[Case Studies](#)
[DDLs](#)
[Downloads](#)
[Drawings](#)
[Line Cards](#)
[Manuals / Instructions](#)
[Product Specifications / Datasheets](#)
[Software](#)
[Specs \(AIA / CSI\)](#)
[Take One](#)
[Tech Notes](#)
[Technical Articles](#)
[Videos](#)
[ez-Biz](#)
[ez-Find](#)
[ez-Learn](#)
[ez-Configurator](#)
[Distribution Home](#)
[Contractor Connection](#)
[ez-Learn](#)
[ez-Find](#)
[Sign In - B2B](#)
[OEM Home](#)
[How to Buy](#)
[Whats New](#)
[Press/News](#)
[Retail Home](#)
[Product Information](#)
[How To](#)
[Merchandising](#)
[Energy Smart Living](#)
[International Home](#)
[China \(English\)](#)
[China \(Chinese\)](#)
[Mexico \(English\)](#)
[Mexico \(Spanish\)](#)
[Middle East \(English\)](#)
[International Contact](#)
[Press](#)
[Products](#)
[Trade Shows](#)
[Made to Order](#)
[EZE-Rough](#)
[Acenti Devices](#)
[AC Switches](#)
[Appliance Switches](#)
[Architectural Controls](#)
[Camera Systems](#)
[Combination Devices](#)
[Connectors & Cables](#)
[Cord Sets](#)
[Corrosion Resistant Devices](#)
[Daylighting Controls](#)
[Decora Devices](#)
[Dimmers](#)
[Cam-Type Devices](#)
[Electrical Accessories](#)
[Entertainment Accessories](#)
[Entertainment Fixtures](#)
[Entertainment Lighting Controls](#)
[Entertainment Lighting Kits](#)



[Electrical](#)
[Network Solutions](#)
[Lighting Controls](#)
[Entertainment](#)
[Home Automation](#)
[Connected Home](#)
[Energy Management](#)
[Power Quality](#)



5269-PLC

Description
15 Amp, 125 Volt, NEMA 5-15R, 2P, 3W, Connector, Straight Blade, Industrial Grade, Grounding, Power Indication – Black-White

- Additional Product Information**
- [Dimensional Drawing](#)
 - [Wiring Diagram](#)


Product Features

Grounding: Grounding
Feature: Power Indication
Amperage: 15 Amp
Voltage: 125 Volt
NEMA: 5-15R
Pole: 2
Wire: 3
Cord Range: .245 – .700
Wire Gauge: 18-10 AWG
Blades/Contacts: Solid Brass
Body Material: Super Tough Nylon
Assembly Screws: Steel, Zinc Plated
Color: Black-White
Standards and Certifications: UL/CSA
Warranty: Lifetime Warranty

Color: Black-White



NEMA: 5-15R



Features and Benefits

- Power Indication Feature: When power is present, the Green Light glows through a lens in the nylon husk.
- The Green Light is factory installed and requires no installation. 15A devices use a neon bulb and 20A to 30A devices use an LED.
- For fast assembly Black & White devices feature:
 - Backed-out, color-coded brass terminal screws
 - Deep slotted triple drive face module and cord clamp screws
 - Deep wire wells with transparent wiring chambers
- Single piece 0.035 inch thick contacts with NO rivets for longest life and continuous conductivity
- Nylon face module features Amperage, Voltage, and NEMA configuration molded into face for easy identification and replacement.
- Fluted nylon housing makes it easier to grip with gloves and in debris-laden environments
- Thick-walled, super tough nylon housing resists abuse and impact
- Single piece external cord clamp includes catalogue number and NEMA configuration for easy identification
- External cord clamp accepts wire mesh connection grips
- Connectors ship with standard white and black cord clamp. Color-coded cord clamps available to identify amperage or equipment. Choose from blue, green, yellow, red, and orange.