

MECHANICAL PARTS


TL-192 Eyelet 1/4 Turn Fastener




Instruction example (caulking)

Tool : [T8-1], [T8-2], [T8-AB], [T9-4], [T10-CD]

① Install the eyelet




② Press the eyelet




③ Press the fastener head



④ Tighten up the fastener



Model No.	Material	Net Weight(g)	Code No.
TL-192	Aluminum	0.7	1136



※Refer to the page T-shaped sign fastener for more information.

TL-242 TL-243 / TL-244 1/4 Turn Fastener Hexagon Recessed



Characteristic

No play on a cover and it absorbs vibration by tightening effect of the spring.
While ordinary fastener can be removed with a coin easily, this fastener cannot be removed unless using a hexagonal wrench that suits for preventing a mischief or a crime.



Application

Measuring instruments /
Distribution panels /
Machine tools

Model No.	Part Name	Material	Finish
TL-242/243/244	Fastener	HSK16M	Cr
ST-6/7/8	Spring	SWP	Zn

Model No.	A	B	C	E	F	G	L	P	Net Weight (g)	Code No.	Set (with Spring)			Eyelet (sold separately)	
											Model No.	Included	Net Weight (g)		Code No.
TL-242-1	φ6	1.5	φ10	φ4.5	7.9	1.6	5.5	1.8~2.0	1.6	1701	TL-242-001	ST-6	2.3	1741	GT-6
TL-242-2		2.5			8.4		6.0	2.3~2.5	1.6	1702	TL-242-002		2.3	1742	
TL-242-3		3.0			8.9		6.5	3.0	1.6	1703	TL-242-003		2.3	1743	
TL-243-1	φ7	3.0	φ12	φ5.5	9.8	2.2	7.0	2.4~2.6	2.8	1704	TL-243-001	ST-7	3.9	1744	GT-7
TL-243-2		3.5			10.3		7.5	3.0~3.1	2.8	1705	TL-243-002		3.9	1745	
TL-243-3					10.8		8.0	3.5~3.6	3.1	1706	TL-243-003		4.2	1746	
TL-244-1	φ8	4.0	φ14	φ6.5	11.7	2.8	8.5	3.0~3.2	4.7	1707	TL-244-001	ST-8	6.4	1747	GT-8
TL-244-2		4.5			12.2		9.0	3.5~3.7	4.7	1708	TL-244-002		6.4	1748	
TL-244-3					12.7		9.5	4.0~4.1	4.9	1709	TL-244-003		6.6	1749	

Refer to the page T-shaped sign fastener for more information.



※Size P is a thickness of the plate.