

## 6-outlet, 6-ft cord, 2100 joules, 2 port USB chargers 2.1 amp total, desk clamp mount strip - Protect It! Surge Suppressor

MODEL NUMBER: TLP606DMUSB



### Description

Tripp Lite's TLP606DMUSB offers economical AC surge suppression for protection of workstations, desktop PCs, telecom systems and other sensitive electronics. Built-in AC surge suppression shields connected equipment from damage and performance problems due to transient surges. USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices. TLP606DMUSB offers 6 total outlets, 6 foot cord, 2 USB charging ports and diagnostic LED to warn of suppressor damage. AC suppression rated at 2100 joules shields equipment from surges and line noise. This matte black surge suppressor has clamps that attach to the side of the desk, workbench or table. 2 knobs easily clamp to desk for better accessibility to plugs - 4 standard and 2 adapter spaced plugs. \$40,000 Ultimate Lifetime Insurance (USA & Canada Only).

PLUG/OUTLETS: Input: NEMA5-15P/Output: 6 NEMA5-15R/6-ft. AC line cord

ELECTRICAL: 120V AC, 50/60Hz, 15A (Requires NEMA5-15R wall receptacle)

FORMAT: Corded multi-outlet strip with 1 transformer spaced outlet

SUPPRESSION: AC: 150V RMS Clamping/2100 joules/400V UL1449 3rd Edition

### Features

- 6 outlets
- 6-ft. cord
- 2 USB charging ports - 2.1 amp total
- Surge suppression rating: 2100 joules
- Clamps for attaching to desk, workbench or table
- EMI/RFI noise filtering
- 15 amp resettable circuit breaker
- Green protection LED
- Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
- Can accommodate 2 large transformer plug without covering remaining outlets.
- 2 knobs to clamping to desk Lighted power switch

### Highlights

- 6 outlet / 6-ft. cord
- 2100 joule rating
- 2.1 amp dual port USB charger
- Clamps to attach to desk, workbench or table
- \$40,000 Ultimate Lifetime Insurance (USA, Puerto Rico & Canada only)

### Applications

- Ideal for any desktop, network or home computing application requiring AC line protection.
- USB charging ports offer fast charging for smartphones, tablets, MP3 players and other portable devices

### Package Includes

- TLP606DMUSB surge suppressor
- Instruction manual with warranty information



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

- \$40,000 Ultimate Lifetime Insurance (USA and Canada Only)

## Specifications

| OVERVIEW                           |                                                                                    |
|------------------------------------|------------------------------------------------------------------------------------|
| Intended Application               | Home/Office                                                                        |
| OUTPUT                             |                                                                                    |
| Frequency compatibility            | 50 / 60 Hz                                                                         |
| Output watts                       | 1875                                                                               |
| Circuit Breaker (amps)             | 15                                                                                 |
| Overload protection                | 15A resettable illuminated combo switch / circuit breaker                          |
| Outlet quantity / type             | 6 NEMA 5-15R                                                                       |
| Transformer accommodation          | Supports 2 large transformer plug accessory without covering remaining outlets.    |
| Outlet orientation                 | Single row of 6 outlets                                                            |
| USB Charging Ports                 | Yes                                                                                |
| INPUT                              |                                                                                    |
| Nominal Input Voltage(s) Supported | 120V AC                                                                            |
| Recommended Electrical Service     | 120V (110-125V)                                                                    |
| Input connection type              | NEMA 5-15P                                                                         |
| Input cord length (ft.)            | 6                                                                                  |
| Input cord length (m)              | 1.83                                                                               |
| Input cord gauge, type             | 14 gauge, SJT                                                                      |
| Voltage compatibility (VAC)        | 120                                                                                |
| Maximum Surge Amps                 | 35500                                                                              |
| LEDS ALARMS & SWITCHES             |                                                                                    |
| Switches                           | Combination AC circuit breaker and 2 position red illuminated on/off power switch  |
| Diagnostic LEDs                    | Built-in LED confirms suppressor "protection present" (green) status               |
| SURGE / NOISE SUPPRESSION          |                                                                                    |
| AC suppression joule rating        | 2100                                                                               |
| AC suppression response time       | < 1 ns                                                                             |
| Protection modes                   | Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression |
| Clamping voltage (RMS)             | 150                                                                                |



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                     |                                              |
|-------------------------------------|----------------------------------------------|
| UL1449 let through rating           | 400V                                         |
| <b>DATALINE SURGE SUPPRESSION</b>   |                                              |
| Cable (Coax) Protection             | No                                           |
| Network (Ethernet) Protection       | No                                           |
| <b>PHYSICAL</b>                     |                                              |
| Material of construction            | Plastic                                      |
| Housing Color                       | Black                                        |
| Receptacle Color                    | Black                                        |
| AC line cord color                  | Black                                        |
| Style                               | Desk Mount Strip                             |
| <b>CERTIFICATIONS</b>               |                                              |
| UL1449 3rd Edition (AC Suppression) | UL1449 3rd EDITION                           |
| UL1363 (Power Tap)                  | UL1363                                       |
| cUL / CSA (Canada)                  | cUL                                          |
| Approvals                           | Exceeds IEEE 587 category A&B specifications |
| <b>WARRANTY</b>                     |                                              |
| Product Warranty Period (Worldwide) | Lifetime limited warranty                    |

© 2014 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tripp Lite:](#)

[TLP606DMUSB](#)