




+ PASSIVE COMPONENTS

THROUGH-HOLE RESISTORS



✓ Active

TE CONNECTIVITY (TE)

FCB6 R50 10% HP

CGS | FC

FCB6R50K

TE Internal Number: 1-1623715-7

[EU RoHS Compliant](#)

[EU ELV Compliant](#)

Resistor Type Power Resistor

Dimensions (mm) 34.4 x 5

Number of Terminations 2

Packaging Method Loose Piece - Box

Tolerance 10%

PRODUCT DRAWING

English

DOCUMENTATION

Product Drawings

HIGH POWER RESISTORS SERIES FCB6 (HIGH PROFILE STANDOFF)

[PDF \(TIFF AVAILABLE\)](#)

English

Catalog Pages/Data Sheets

1309350_PASSIVE_COMPONENT

PDF

English

High Power Resistors - Type FC Series - Tyco Electronics Passives

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Resistor Type Power Resistor

Element Type Wirewound

Product Type Fixed Resistor

Configuration Features

Number of Resistors 1

Electrical Characteristics

Tolerance 10%

Resistance Range Up to 1kΩ

Resistance (Ω) .5

Power Rating (W) 5

Body Features

Lead Type Axial Leaded

Termination Features

Number of Terminations 2

Termination Type Tinned Plated Brass

Mechanical Attachment

Mount Style Pluggable

Dimensions

Dimensions (mm) 34.4 x 5

Usage Conditions

Temperature Coefficient (ppm/°C) ±400, ±50

Packaging Features

Packaging Method Loose Piece - Box

Statement of Compliance

Statement of Compliance

PDF
