



# Heyco® Nylon Cable Clamps

Light Duty—3/8" (9,5mm) Wide, .050" (1,3mm) Thick

- For clamping cable or tubing securely into place.
- All parts are size marked in inches and millimeters.
- Resists corrosion, salt water, weak acids, gasoline, alcohol, oil, grease, and common solvents. This feature is not assessed by UL certification or testing.
- See page 4-20 for Arrow Clips and Push-In Fasteners suitable for securing Heyco Cable Clamps.
- Molded in natural, black or 94 V0 halogen free polyamide.



MOUNTING HOLE DIAMETER		SCREW SIZE	PART NO.		94V-0 HALOGEN FREE	DESCRIPTION	PART DIMENSIONS A	
in.	mm.		Black	Natural			in.	mm.
.170	4,3	8	3362	3312		CCL 125-170	.125	3,2
			3363	3313		CCL 187-170	.187	4,7
			3364	3314		CCL 250-170	.250	6,3
			3365	3315		CCL 312-170	.312	7,9
			3366	3316		CCL 375-170	.375	9,5
			3367	3317		CCL 437-170	.437	11,1
			3368	3318		CCL 500-170	.500	12,7
			3352	3302	3873	CCL 1/8	.125	3,2
.203	5,2	10	3353	3303	3874	CCL 3/16	.187	4,7
			3354	3304	3875	CCL 1/4	.250	6,4
			3355	3305	3876	CCL 5/16	.312	7,9
			3356	3306	3877	CCL 3/8	.375	9,5
			3357	3307	3878	CCL 7/16	.437	11,1
			3358	3308	3879	CCL 1/2	.500	12,7

**Heyco LabKit No. 5 (Part #3399)** contains 285 nylon cable clamps in 18 different sizes, both standard and heavy duty for 1/8" (3,2mm) to 1-1/2" (38,1mm) diameter applications. See page 4-21.

# Heavy Duty—1/2" (12,7mm) Wide, .060" (1,5mm) Thick

MOUNTING HOLE DIAMETER		SCREW SIZE	PART NO.		DESCRIPTION	PART DIMENSIONS A	
in.	mm.		Black	Natural		in.	mm.
.203	5,2	10	3372	3322	CCH 1/8	.125	3,2
			3373	3323	CCH 3/16	.187	4,7
			3374	3324	CCH 1/4	.250	6,4
			3375	3325	CCH 5/16	.312	7,9
			3376	3326	CCH 3/8	.375	9,5
			3377	3327	CCH 7/16	.437	11,1
			3378	3328	CCH 1/2	.500	12,7
			3379	3329	CCH 9/16	.562	14,3
			3380	3330	CCH 5/8	.625	15,9
			3381	3331	CCH 11/16	.687	17,4
			3382	3332	CCH 3/4	.750	19,1
			3383	3333	CCH 13/16	.812	20,6
			3384	3334	CCH 7/8	.875	22,2
			3390	3340	CCH 1	1.000	25,4
			3392	3342	CCH 1-1/8	1.125	28,6
			3393	3343	CCH 1-3/16	1.187	30,1
			3394	3344	CCH 1-1/4	1.250	31,8
			3396	3346	CCH 1-3/8	1.375	34,9
			3398	3348	CCH 1-1/2	1.500	38,1

Standard Colors: Black or Natural. Other colors available at extra charge (minimum quantities apply).



Quick Specs

Material	6/6 "Nylon"
Certifications	Recognized under the Component Program of Underwriters' Laboratories File #E-54523
Flammability Rating	94V-2
Material Temperature Index	125°C—Maximum temperature on part not to exceed 105°C