






- NOTES
1. ALL DIMENSIONS IN MM
 2. GENERAL TOLERANCE: X.X=±0.4, X.XX=±0.25
 3. TERM NOS FOR REF ONLY.
 4. RATING: 30VDC, 0.3A
 5. OPERATING FORCE: 330±100GF
 6. TRAVEL: FULL 3.5MM; LOCK 2.5MM
 7. CONTACT RESISTANCE: 100 MILLI-Ω MAX
 8. INSULATION RESISTANCE: 500VDC-100 MEGA-Ω MIN
 9. WITHSTAND VOLTAGE: 500VAC FOR 1 MINUTE
 10. OPERATING TEMP: -20° TO 80°C
 11. ELECTRICAL LIFE: 10,000 CYCLES MIN
 12. TIMING: SHORTING (MBB)

E-SWITCH®

REV.		ECN No.	DESCRIPTION	DATE	CHKD
A		11534	RELEASED FOR PRODUCTION	6/8/01	CJB
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
TITLE		SCALE		DATE	
LC2258 EE SP (LATCHING)		3:1		6/8/01	
REV.		DR		DWG	
A		CJB		P070215	