

Amphenol Connex Crimp Tooling

Connex 47 Series Coax Crimp Tools utilize industry standard crimp die set dimensions. Tool handle can be purchased separately or with die set pre-installed. Die sets listed below will terminate all popular coaxial cables. Full ratchet crimp action ensures ferrules and contacts are fully crimped before tool releases.

Code	Crimp Tool & Die Set	Die Set Only	Hex Crimp Dimension (Inches)																Applicable Cable Types
			.042	.052	.068	.080	.100	.118	.128	.151	.178	.190	.213	.255	.263	.278	.320	.324	
A	47-10070	47-20000			•								•	•					RG 55/58/59/62/141/142/233/303/400/8X LMR195/200/240
B	47-10150	47-20004			•				•		•								RG 174/188/316/179/187/180/195/178/196 LMR100
C	47-10160	47-20008								•	•		•						.151 Hex 316/179/ Double Braid
D1	47-10090	47-20003				•	•												• RG 8/11/213/214/225/393/N Series
D2	47-10230	47-20029					•						•						• RG 8/11/213/214/225/393/58/141/223/55/142/400/8X LMR240
E	47-10110	47-20001	•		•									•			•		RG 6/59/B8281
F	47-10120	47-20002	•		•						•		•						RG 58/174/188/316/179/187/142/141/223/400/55
G	47-10063	47-20245	•		•							•	•						RG 58/59/ Plenum
H	47-10100	47-20026												•			•	•	RG 59/ 6-FCATV
J	47-10180	47-20025		•	•		•						•	•					5 Cavity RG 58/59N, BNC, TNC, SMA
K	47-10200	47-20024			•						•							•	RG 6/B8218/174/188/316/179/187
L	47-10210	47-20027						•											• LMR 400/B9913/9914/b7810A
M	47-10220	47-20028		•	•						•			•					RG 59/62/174/188/316/179/187
N	47-10240	47-20030	•		•									•		•			B1505A/B1694A (For Kings 2065-10-9)
O	47-10250	47-20247					•		•	•									178/195/174/316/188/179/187/316/316, Double Braid
P	47-10260	47-20249			•		•												• RG8/11/213/214/393 BNC, TNC, N
R	47-10270	47-20250	•		•				•		•								BNC/TNC/.068 And .042 Crimp Center Contact
S	47-10280	47-20251		•											•				BNC/TNC RG 6U
T	47-10290	47-20252		•												•			1.0/2.3 DIN



Crimp Frame P/N: 47-10000

For use with all die sets listed above



4- Way Indent Crimp Tool: 47001

For use with BNC, TNC and N connectors that feature the pin-in-pin contact termination.

12-Way Indent Crimp Tool: 47009

Full ratchet crimp tool terminates precision BNC 0.053" diameter 75 ohm center conductor.



**LMR 500/600 Hand Tool
w/ 0.610" Hex Die Set
P/N: 47021**

Additional options available. Contact us for details.

Contact Us at (800) 942-6639

www.amphenolconnex.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[47-10110](#) [47-10210](#) [47-10090](#) [47001](#) [47-10150](#) [47-10070](#) [47-10180](#) [47-10160](#) [47-10120](#) [47-10200](#) [47-10230](#)
[47-10240](#) [47-10250](#) [47-10270](#) [47-20024](#) [47-20025](#) [47-20029](#) [47-20030](#) [47-20249](#) [47-20250](#) [47009](#)