



TLS 2200® / TLS PC Link™ Wire and Cable Marking

► PERMASLEEVE™ WIRE MARKING SLEEVES

Heat-Shrinkable White Polyolefin (B-342)



Part Number	Sleeves Per Roll	Sleeve Dimensions		Range of Wire Dia.		Approx. Wire Gauge*	Maximum Characters Per Line For Font: 2	Maximum Lines Of Text For Font: 2
		A Inch (mm)	B Inch (mm)	Min	Max			
1.015" Marker Width								
WHITE 3:1 SHRINK RATIO								
PSPT-094-1-WT	100	1.015 (25.78)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	22	1
BPSPT-094-1-WT	2500	1.015 (25.78)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	22	1
PSPT-125-1-WT	100	1.015 (25.78)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	22	1
BPSPT-125-1-WT	1000	1.015 (25.78)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	22	1
PSPT-187-1-WT	100	1.015 (25.78)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	22	2
BPSPT-187-1-WT	1000	1.015 (25.78)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	22	2
PSPT-250-1-WT	100	1.015 (25.78)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	22	3
BPSPT-250-1-WT	1000	1.015 (25.78)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	22	3
PSPT-375-1-WT	100	1.015 (25.78)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	22	5
BPSPT-375-1-WT	1000	1.015 (25.78)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	9	5
PSPT-500-1-WT	100	1.015 (25.78)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	22	7
BPSPT-500-1-WT	100	1.015 (25.78)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	22	7
PSPT-1000-1-WT	50	1.015 (25.78)	1.660 (42.16)	0.450 (11.43)	0.950 (24.13)	1-500	22	16
YELLOW 3:1 SHRINK RATIO								
PSPT-094-1-YL	100	1.015 (25.78)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	22	1
PSPT-125-1-YL	100	1.015 (25.78)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	22	1
PSPT-187-1-YL	100	1.015 (25.78)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	22	2
PSPT-250-1-YL	100	1.015 (25.78)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	22	3
PSPT-375-1-YL	100	1.015 (25.78)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	22	5
PSPT-500-1-YL	100	1.015 (25.78)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	22	7
PSPT-1000-1-YL	50	1.015 (25.78)	1.660 (42.16)	0.450 (11.43)	0.950 (24.13)	1-500	22	16
1.765" Marker Width								
WHITE 3:1 SHRINK RATIO								
PSPT-094-175-WT	100	1.765 (44.83)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	41	1
BPSPT-094-175-WT	2500	1.765 (44.83)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	41	1
PSPT-125-175-WT	100	1.765 (44.83)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	41	1
BPSPT-125-175-WT	1000	1.765 (44.83)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	41	1
PSPT-187-175-WT	100	1.765 (44.83)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	41	3
BPSPT-187-175-WT	1000	1.765 (44.83)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	41	3
PSPT-250-175-WT	100	1.765 (44.83)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	41	3
BPSPT-250-175-WT	1000	1.765 (44.83)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	41	3
PSPT-375-175-WT	100	1.765 (44.83)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	41	5
BPSPT-375-175-WT	1000	1.765 (44.83)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	41	5
PSPT-500-175-WT	100	1.765 (44.83)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	41	7
BPSPT-500-175-WT	1000	1.765 (44.83)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	41	7
PSPT-1000-175-WT	50	1.765 (44.83)	1.660 (42.16)	0.450 (11.43)	0.950 (24.13)	1-500	41	16
BPSPT-1000-175-WT	500	1.765 (44.83)	1.660 (42.16)	0.450 (11.43)	0.950 (24.13)	1-500	41	16
YELLOW 3:1 SHRINK RATIO								
PSPT-094-175-YL	100	1.765 (44.83)	0.182 (4.62)	0.023 (0.58)	0.080 (2.03)	28-18	41	1
PSPT-125-175-YL	100	1.765 (44.83)	0.235 (5.96)	0.046 (1.17)	0.110 (2.79)	22-16	41	1
PSPT-187-175-YL	100	1.765 (44.83)	0.335 (8.50)	0.062 (1.57)	0.150 (3.81)	18-12	41	3
PSPT-250-175-YL	100	1.765 (44.83)	0.439 (11.15)	0.094 (2.39)	0.215 (5.46)	16-10	41	3
PSPT-375-175-YL	100	1.765 (44.83)	0.645 (16.38)	0.125 (3.18)	0.320 (8.13)	12-6	41	5
PSPT-500-175-YL	100	1.765 (44.83)	0.851 (21.61)	0.187 (4.75)	0.450 (11.43)	8-1	41	7
PSPT-1000-175-YL	50	1.765 (44.83)	1.660 (42.16)	0.450 (11.43)	0.950 (24.13)	1-500	41	16

* Based on National Electric Code insulation measurement of THHN Wire.

Note: Labels are sorted in order by width, height, 3 digit material number (within part number), then die number (within part number).

► DURASLEEVE® WIRE MARKER SLEEVES

DuraSleeve White Polypropylene Inserts (B-390)

Part Number	Sleeves Per Roll	Sleeve Dimensions	
		Inch Width (mm)	Inch Height (mm)
PTDS-15-390	300	0.590 (15.00)	0.163 (4.14)
PTDS-30-390	300	1.181 (30.00)	0.163 (4.14)
BPTDS-15-390	3000	0.590 (15.00)	0.163 (4.14)
BPTDS-30-390	3000	1.181 (30.00)	0.163 (4.14)