








RECOMMENDED P.C.B. PATTERN LAYOUT

NOTE:  
 MATERIAL:  
 HOUSING:PBT+30% G.F. UL 94V-0  
 CONTACT:BRASS  
 SHELL:SPCC  
 PLATING:  
 CONTACT: GOLD FLASH AND TIN OVER NICKEL PLATED  
 SHELL: NICKEL PLATED OVER ALL  
 SPECIFICATION:  
 CURRENT-MAX[AMPS]:1.5A  
 VOLTAGE-MAX[VOLTS]:30V  
 WITHSTANDING VOLTAGE: 500V AC  
 CONTACT RESISTANCE[OHMS]:30 milliohms max  
 INSULATION RESISTANCE[OHMS]: 1000 MEGOHMS MIN  
 ENVIRONMENTAL  
 TEMPERATURE RANGE -55°C~+85°C  
 PART NO.:

|                                                     |        |                |              |  |                                    |                      |
|-----------------------------------------------------|--------|----------------|--------------|--|------------------------------------|----------------------|
| 09/03/20                                            | SYSTEM |                | NEW DWG      |  |                                    | AO                   |
| DATE                                                | DR.BY  | ECN.NO.        | DESCRIPTION  |  | MARK                               | VER.                 |
| -TOLERANCES-<br>UNLESS OTHERWISE SPECIFIED<br>公差參考表 |        |                | CnC Tech,LLC |  |                                    |                      |
|                                                     |        |                |              |  | TITLE: USB 4P A/M DIP<br>90° 1U"成品 |                      |
| X.X                                                 | ±0.30  | X.X° ±3.00°    | APPD:        |  | PRODUCT NO: 1001-010-01001         |                      |
| X.XX                                                | ±0.15  | X.XX° ±1.00°   | CHECK:       |  | DATE                               | SCALE UNIT TYPE PAGE |
| X.XXX                                               | ±0.100 | X.XXX° ±0.500° | DRAW:        |  | 2009.03.20                         | 1:1 mm CD 1 / 1      |