

M6 3W 2390 LED

www.pelicanproducts.us



M6 3W 2390 LED Flashlight





Bright light. Tough body. The M6 2390 Flashlight uses a 3 watt Cree LED for intense brightness. The strong body is CNC-machined aluminum with knurled grip for a secure handle. Plus, it has a Type III anodized coating for extra protection. The convenient push button tail cap switch has a safety lockout feature to prevent inadvertent battery depletion or accidental activation. The M6 comes with a free Cordura® holster with back-up battery pouch. 2 CR123 lithium cells are also included.

Minimum Pack 6 ea.

Packaged Weight: 10.0 oz.

M6 3W 2390 LED Flashlight Specifications

	High	
LIGHT SOURCE	LED	
BATTERIES	2 CR123 Lithium (Included)	
CHARGE TIME	N/A	
VOLTAGE	6	
LENGTH	5.31" (13.5 cm)	
WEIGHT w/ BATTERIES	5.6 oz. (0.16 kg)	
WEIGHT w/o BATTERIES	4.4 oz. (0.12 kg)	

	FL1 STANDARD	High	
LIGHT OUTPUT		177 LUMENS	
RUNTIME (hours/min)		2h 30m	
BEAM DISTANCE (meters)		155m	
PEAK BEAM INTENSITY (candela)		6002cd	

M6 3W 2390 LED Flashlight Configurations

Cat. #	Description
2390	M6 3W 2390 LED Flashlight (Boxed)

M6 3W 2390 LED Flashlight Accessories

Cat. #	Description
610	Front Sight Mount
620	Side Sling Mount
630	Foregrip Mount
770	Universal Helmet Light Holder
2326	Remote Pressure Switch
2327	Cordura® Holster
2322OR	Traffic Wand (Orange)
2322YW	Traffic Wand (Yellow)
2325BLUE	M6 Blue Filter Cap
2325RED	M6 Red Filter Cap