

STRAIGHT KNURL 30-50 TPI

4.50 [.177]

21.00 [.827]

3.81 [.150]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex										
8						DRAWN	GRS	04/20/08												
7						CHECKED														
6						ISSUED				PART DESCRIPTION										
5						SHEET		1 OF 1		BNC JACK TO MCX JACK ADAPTER										
4																				
3	CONTACT PIN	BER. COPPER	GOLD	1						PART NO.										
2	INSULATOR	PTFE	NATURAL	1						242206										
1	BODY	BRASS	GOLD	1	CAD FILE				C:/242/242206.DWG		DWG. NO.		242206.DWG		REV.	A	SIZE	A	SCALE	NA
	DESCRIPTION	MATERIAL	FINISH	QTY																