

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [1300530002](#)  
**Status:** **Active**  
**Overview:** [Brad® Industrial Ethernet Solutions](#)  
**Description:** Brad® RJ-Lnxx® R-J45 110 Punchdown Ethernet Receptacle, with Hex Nut and Bulkhead Gasket, 1" - 14 UNC Threads, 0.056m (2.19") Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family Industrial Receptacles  
Series [130053](#)  
IP Rating IP67  
NEMA Rating NEMA 6  
Overview [Brad® Industrial Ethernet Solutions](#)  
Product Name Brad®, RJ-Lnxx®  
Type 110 Punchdown  
UPC 78678846635

**Physical**

Coupling Type External Thread  
Gender Female  
Keyway None  
Length 0.056m  
Material - Component ABS  
Mounting Thread Size 1" - 14 UNC  
Net Weight 24.500/kg  
Orientation Straight  
Panel Mount Front  
Poles N/A  
Temperature Range - Operating -20°C to +80°C  
Wire Size AWG N/A  
Wire/Cable Type N/A

**Electrical**

Current - Maximum per Contact 1.5A  
Voltage - Maximum 125V DC

**Material Info**

Old Part Number ENDR2FB5

**Reference - Drawing Numbers**

Sales Drawing SD-130053-002



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Relevant**

**China RoHS**

**REACH SVHC**

Not Relevant

**Halogen-Free**

**Status**

**Not Relevant**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

|            |              |
|------------|--------------|
| China ROHS | Not Relevant |
| ELV        | Not Relevant |

**Search Parts in this Series**

[130053](#) Series

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION