

Thermocouples

Thermocouples are an accurate yet inexpensive sensor for measuring temperatures. The Pico range of Type K thermocouples are ideal for industrial and educational use.

Thermocouple Quick Select

Cat No	Type	Temperature Range (°C)									
		-100	-50	0	50	100	150	200	250	300	350
SE000	Exposed wire										
SE001	Exposed wire										
SE002	Air										
SE003	Insertion										
SE004	Ribbon surface										

Type K Thermocouple (Exposed Wire, PTFE Insulated)



- Tip diameter: 1.5 mm
- Tip temperature: -75 to +250 °C

Cat No	Length
SE000	1 metre
SE027	2 metres
SE028	3 metres
SE029	10 metres

Type K Thermocouple (Exposed Wire, Fibreglass Insulated)



- Tip diameter: 1.5 mm
- Tip temperature: -60 to +350 °C

Cat No	Length
SE001	1 metre
SE030	2 metres
SE031	5 metres

SE002: Type K Thermocouple (Air Probe)



- Tip diameter: 4.5 mm
- Tip temperature: -50 to +250 °C
- Probe length: 120 mm

SE003: Type K Thermocouple (Insertion Probe)



- Tip diameter: 3.33 mm
- Tip temperature: -50 to +250 °C
- Probe length: 120 mm

SE004: Type K Thermocouple (Ribbon Surface Probe)



- Tip diameter: 8 mm
- Tip temperature: -10 to +250 °C
- Probe length: 120 mm