



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECO-08-032010	26MAR09	HMR	MS
	G	REVISED PER ECO-16-006378	03NOV2016	RS	MZ


1 HOUSING, ADAPTER AND PRESSURE PLATE: NYLON, BLACK.
WIRE ENTRY SEAL: ELASTOMER, RED-IRON OXIDE.
PERIPHERAL SEAL: ELASTOMER, GRAY.

2 CONNECTOR WILL ACCEPT (16) MULTIMATE PIN CONTACTS.

3 PART NUMBER STAMPED ON EITHER STRAIGHT EDGE, AS INDICATED.



OBSOLETE	.040 — .080	SMALL	796276-3
	.040 — .080	SMALL	796276-2
	.065 — .100	STANDARD	796276-1
	WIRE INSULATION DIAMETER RANGE	INSULATION	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. McEACHIN 27-JAN-2000		 TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK K. DOWHOWER 27-JAN-2000					
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH	APVD K. DOWHOWER 27-JAN-2000		NAME ASSEMBLY, RECEPTACLE, STANDARD SEX, 17-16, STANDARD OR SMALL INSULATION DIA., SEALED			
		PRODUCT SPEC —					
MATERIAL 		APPLICATION SPEC —		SIZE A2	CAGE CODE 00779	DRAWING NO C=796276	RESTRICTED TO —
		WEIGHT		CUSTOMER DRAWING			SCALE 2:1