







GENERAL TOLERANCE										USED ON
10 MAX	30 MAX	50 MAX	70 MAX	100 MAX	120 MAX	250 MAX	250 OVR	ANGLE	ECCENT	
±0.15	±0.20	±0.30	±0.40	±0.50	±0.75	±0.90	±1.4	±0.5°	0.1	



- NOTES:
1. MATERIALS: POLYESTER (PBT), GLASS FILLED, UL94V-0
 2. MATES WITH: 502352, 560020 SERIES
 3. APPLICABLE TERMINAL : 560124-0101, 560124-0131
 4. APPLICABLE ISL : 560125-0400
 5. GENERAL TOLERANCES : SEE TABLE
 6. EVL AND RoHS COMPLIANT
 7. PRODUCT SPECIFICATION: PS-560123-001
 8. PACKING SPECIFICATION: PK-560123-001

ORDER NO.	MATERIAL NO.	COLOR
560123-0400	5601230400	WHITE
560123-0401	5601230401	BLACK
560123-0402	5601230402	RED
560123-0404	5601230404	BLUE

ADDED OPTION				QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	
EC NO: KTR2016-0056				DESCRIPTION				MM ONLY				NEW 2.0 PITCH W/B CONN. REC. 4WAY HSG DURACLIK™ ISL SERIES MOLEX INCORPORATED	
2016/02/23						mm	INCH	DRAWN BY		DATE	TITLE		
DRWNS:JLEE06						4 PLACES	± ---	± ---	YIBAOK		2014/07/03		
2016/02/23						3 PLACES	± ---	± ---	CHECKED BY		DATE		
CHKD:BCY00N						2 PLACES	± ---	± ---	BCY00N		2014/07/03		
2016/02/25						1 PLACE	± ---	± ---	APPROVED BY		DATE		
APPR: JYCH01						ANGULAR		± ---°	SRTAK		2014/08/26		
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO.		DOCUMENT NO.		SHEET NO.	
				SEE TABLE				SD-560123-002		1 OF 1			
C				REV				SIZE	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
								A3					