






2		1							
LOC	DIST	REVISIONS							
J	—	変更							
		P	LTR	DESCRIPTION			DATE	DWN	APVD
			R	REVISED PER ECO-15-002720			02MAR2015	AP	SB



- 1 MATERIAL AND FINISH
PLUG HOUSING
; THERMOPLASTIC (UL94V-0) COLOR:BLACK
REC. CONTACT
; COPPER ALLOY FINISH,OVER NICKEL
MATING END:0.0002 MIN. OR
0.00076 MIN. GOLD
TERMINATION END:TIN
OVER SEALING TREATMENT.
- 2 P.C.B. LAYOUT AND P.C.B. TREATMENT(REF.)
USE A P.C.B. SURFACE ARE TREATED WITH SOLDER RESIST.
- 3 KINK POSITIONS(4 POSITIONS).
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI



OBSOLETE OBSOLETE		Au PL. 0.00076 MIN.	96	49	59.69	63.86	71.00	47	96	6—	—8
			68	35	41.91	46.08	53.22	33	68	6—	—7
			48	25	29.21	33.38	40.52	23	48	6—	—6
			34	18	20.32	24.49	31.63	16	34	6—	—5
OBSOLETE OBSOLETE		Au PL. 0.0002 MIN.	96	49	59.69	63.86	71.00	47	96		—8
			68	35	41.91	46.08	53.22	33	68		—7
			48	25	29.21	33.38	40.52	23	48		—6
			34	18	20.32	24.49	31.63	16	34	—5174681—	—5
REMARK		N	M	A		B	C	n	POS.	PART NO.	
		CIRCUIT NO.		DIMENSION							

GENERAL TOLERANCE
一般公差

10 ≥ : ±0.2
30 ≥ > 10: ±0.25
100 ≥ > 30: ±0.3
ANGLES: ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -
MATERIAL 材料	FINISH 仕上

DWN T.KAWAMAE 18JAN05	TE Connectivity			
CHK I.ENOMOTO 18JAN05				
APVD I.ENOMOTO 18JAN05	NAME 名称			
PRODUCT SPEC 製品規格 108-60036	PLUG ASSY VERTICAL (W/KINK) AMPLIMITE .050 SERIES I B-TO-B CONN.			
APPLICATION SPEC 取付適用規格				
WEIGHT	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-5174681	RESTRICTED TO —
CUSTOMER DRAWING		SCALE 尺度 2:1	SHEET 1 OF 1	REV R