


LOC		DIST	REVISIONS					
-		-	P	LTR	DESCRIPTION	DATE	DWN	APVD
				A	ECO-06-23628	25OCT2006	MB	MW



NOTES:

- KEY REMOVABLE IN OFF POSITION ONLY.
- KEYSWITCH SUPPLIED WITH 1 HEX NUT, 1 DRESS NUT AND 1 KEY.
- WIRE: 18 AWG BOND WIRE, TINNED, PVC INSULATED, W/ 80°C AND 300 V RATING (UL 1007).
CONTACT MATERIAL: MOVABLE-BRONZE, SILVER PLATED;
STATIONARY-BRASS, SILVER PLATED.
CIRCUIT: SPST
ACTION: OFF-ON
- ELECTRICAL SPECIFICATIONS:
KEYSWITCH RATING: 6A, 125V AC; 3A, 250V AC
DIELECTRIC VOLTAGE: 1000V RMS MIN.
INSULATION RESISTANCE: 100 MΩ MIN.
CONTACT RESISTANCE: 100 mΩ MAX.
CYCLE LIFE: 6000 OPERATIONS MIN.
TEMPERATURE RISE: <30°C AT 6000 OPERATIONS
- ENVIRONMENTAL SPECIFICATIONS:
OPERATING TEMP: -18°C TO 65°C

THIS DRAWING IS UNPUBLISHED.
COPYRIGHT 20
©

1571487-1	PART NUMBER
-----------	-------------

DIMENSIONS: INCHES		DWN	12NOV2003	MATERIAL	-	FINISH	-	
		CHK	07NOV2006	tyco Tyco Electronics Harrisburg, PA 17105-3608				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± 1 PLC ±.03 2 PLC ±.015 3 PLC ±.010 4 PLC ± ANGLES ±1/2		APVD	07NOV2006					
		PRODUCT SPEC			NAME			
		-			KEYSWITCH, SPST			
		APPLICATION SPEC			RESTRICTED TO			
		-						
		WEIGHT		CAGE CODE		DRAWING NO		
		-		A4 00779C		G=1571487		
CUSTOMER DRAWING				SCALE		SHEET	REV	
				3:4		1 OF 1	A	