



Search supplies & accessories (1)

Enter all or first part of keyword(s) or part number

Searches products from HP and other leading brands

[Computing accessories](#) > [Networking](#) > [Switches](#) > [Access switches - fixed port unmanaged](#)

HP 1410-24G Switch

[Enlarge Image](#)

MFG#J9561A#ABA

Quantity: [Add to Cart»](#)

Shopping for...

- » Computing accessories
- » Printing supplies & Accessories
- » Software solutions
- » Specials & Promotions

Help me find...

- » Memory finder
- » Services & Support finder

Shop by brand...

- » HP
- » APC
- » Belkin
- » C2 G
- » Ergotron
- » Getac
- » Kensington
- » Kingston
- » Linksys
- » Logitech
- » Microsoft
- » Motorola
- » Samsung
- » Targus
- » ViewSonic

Shop by other brands...

- Select brand [»](#)
- » Manufacturer directory
 - » Advanced search
 - » Search tips

[» Overview](#) [Specs](#) [» What is in the box](#) [» Related products](#)

Product Documents:

Specifications - HTML [»](#)

Address table size	8000 entries
Form Factor	1U height
Input Frequency	50/60 Hz
Input Operating Current	0.3/0.2 A
Input Voltage	100-127/200-240 VAC
Manufacturer Warranty	Lifetime, advance replacement , next business day
Ports	22 autosensing 10/100/1000 ports(IEEE 802.3 Type 10BASE-T, IEEE 802.3u Type 100BASE-TX, IEEE 802.3ab Type 1000BASE-T), Media Type: Auto-MDIX, Duplex: 10BASE-T/100BASE-TX: half or full; 1000BASE-T: full only; 2 dual-personality ports, each port can be used as either an RJ-45 10/100/1000 port (IEEE 802.3 Type 10Base-T; IEEE 802.3u Type 100Base-TX; IEEE 802.3ab 1000Base-T Gigabit Ethernet) or an open mini-GBIC slot (for use with mini-GBIC transceivers)
Power consumption	22 W (maximum)
Product dimensions (W x D x H)	13.23 x 6.65 x 1.73 in
Technical Notes	Use only supported genuine HP mini-GBICs with your switch.
Warranty	Lifetime, advance replacement , next business day
Weight (Imperial)	2.98 lb
Weight (Metric)	1.35 kg

Extended specifications

Interfaces/Ports	
Total Number of Network Ports	24
Number of Network (RJ-45) Ports	24
Media & Performance	
Network Technology	10/100/1000Base-T
Ethernet Technology	Gigabit Ethernet
I/O Expansions	
Number of Total Expansion Slots	2
Number of SFP Slots	2
Expansion Slot Type	SFP
Shared SFP Slot	Yes
Network & Communication	
Layer Supported	2
Management & Protocols	
Manageable	No

Power Description

Input Voltage	110 V AC 220 V AC
Power Source	Power Supply

Physical Characteristics

Form Factor	Rack-mountable Wall Mountable Desktop
Height	1.7"
Width	13.2"
Weight (Approximate)	2.98 lb
Depth	6.7"

Miscellaneous

Green Compliant	Yes
Green Compliance Certificate/Authority	WEEE REACH

Warranty

Standard Warranty	Lifetime
--------------------------	----------

Product Documents:

[Specifications - HTML](#)[» Return to original page](#)