




CIRCUIT: SPST

CONTACT CONFIGURATION



RECOMMEND P.C.B. LAYOUT



NOTES:

1. ALL DIMENSIONS IN MM
2. TERM. NOS. FOR REF ONLY
3. RATING: DC 12V, 50mA
4. TRAVEL: 0.25±0.1mm
5. CONTACT RESISTANCE: 100 Ohms Max.
6. 2002/95/EC (ROHS) COMPLIANT

REVISED & REDRAWN		DATE		CHKD	
B		7/14/98			
REV.	DESCRIPTION	DATE		CHKD	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					
TOLERANCES		TITLE		SCALE	
0.0	±0.4	TL 1105Q F160 Q (STD. BRACKET)		4:1	
0.00	±0.25				
		DATE		DR	
		1/12/10		BLR	
		DWG		P010022	
		REV		C	

