

Accessories

SFP (Small Form Pluggable)

SFP (Small Form Pluggable)

SFP 100MM

Multi-mode 100Mbps 2KM Fiber Transceiver , commercial operating Temp. 0~ 70°C



Wave-length: 1310nm
Tx Power:
-20dBm(Min)~-14dBm(Max)
Rx Sensitivity: -31dBm(Max)
Linkbudget: 11dBm

Operation Temperature :
-10°C~70°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFP 100MM -w

Multi-mode 100Mbps 2KM Fiber Transceiver, wide operating Temp. -40~ 85°C



Wave-length: 1310nm
Tx Power:
-20dBm(Min)~-14dBm(Max)
Rx Sensitivity: -31dBm(Max)
Linkbudget: 11dBm

Operation Temperature :
-40°C~85°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFP100SM30

Single mode 100Mbps 30KM Fiber Transceiver, Commercial operating Temp. 0~ 70°C



Wave-length: 1310nm
Tx Power:
-15dBm(Min)~-8dBm(Max)
Rx Sensitivity: -34dBm(Max)

Linkbudget: 19dBm
Operation Temperature : 0°C~70°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFP100SM30-w

Single mode 100Mbps 30Km Fiber Transceiver , Wide operating Temp. -40~ 85°C



Wave-length: 1310nm
Tx Power:
-15dBm(Min)~-8dBm(Max)
Rx Sensitivity: -34dBm(Max)
Linkbudget: 19dBm

Operation Temperature :
-40°C~ 85°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFP (Small Form Pluggable)

SFP (Small Form Pluggable)

SFPGSX

1000Base-SX multi-mode transceiver 550m , commercial operating Temp, 0~70°C



Wave-length: 850nm
Tx Power:
-9.5dBm(Min)~-4dBm(Max)
Rx Sensitivity: -18dBm(Max)

Linkbudget: 8.5dBm
Operation Temperature : 0°C~70°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFPGSX-w

1000Base-SX multi-mode transceiver 550m , commercial operating Temp, -40~85°C



Wave-length: 850nm
Tx Power:
-9.5dBm(Min)~-4dBm(Max)
Rx Sensitivity: -18dBm(Max)
Linkbudget: 8.5dBm

Operation Temperature :
-20°C~85°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFPGLX10

1000Base-LX single-mode transceiver 10Km , commercial operating Temp, 0~70°C



Wave-length: 1310nm
Tx Power:
-9.5dBm(Min)~-3dBm(Max)
Rx Sensitivity: -20dBm(Max)

Linkbudget: 10.5dBm
Operation Temperature : 0°C~70°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%

SFPGLX10-w

1000Base-LX single-mode transceiver 10Km , commercial operating Temp, -40~85°C



Wave-length: 1310nm
Tx Power:
-9.5dBm(Min)~-3dBm(Max)
Rx Sensitivity: -20dBm(Max)
Linkbudget: 10.5dBm

Operation Temperature :
-40°C~ 85°C
Storage Temperature: -40°C~85°C
Operating Humidity: 85%