

D series



UL Recognized File E 118235

D series is the standard D.Sub full metal shell version with stamped contacts. This design is basically proposed in solder bucket, straight and angled version without accessories.




Ordering information


Series	D	B	25	P	5	64	C	T	X
Shell size E, A, B, C, D									
Number of contacts 09, 15, 25, 37, 50									
Contacts P : Pin S : Socket									
Termination type 0 : Solder bucket 3 : Straight 5, 8, 9, 14, 18 : Angled									
Plating 64 : ≥ 200 mating / unmating 65 : ≥ 500 mating / unmating (severe environment requirements)									
Options 2 (see cover page 69 bis)									
Termination type Index	Straight version	Angled version	Solder buckets						
Blank	Without accessory	Not possible	Without accessory						
C	Not possible	Without bracket	Not possible						
H*	Not possible	Not possible	Shielding termination fingers*						
* not available on 50 way									
Shell plating T : Standard tin plating									
Dimples X : Standard for male connector only									

Specific dimensions


Solder buckets



Straight spills



Angled spills



Cote	Termination					(U.S. standard) 9
		5	8	14	18	
A		2.54	2.84	2.54	2.84	2.84
B±0.1		10.40	10.40	10.40	10.40	8.10
C±0.3		4.50	4.50	3.90	3.90	3.18
D±0.3	9 to 37	10.70	10.70	10.70	10.70	9.50
	50	12.10	12.10	12.10	12.10	10.80

Note: for other requirement, consult us.