



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT - By - ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-		A	INITIAL RELEASE	12NOV2013	GSK	BvH
			A1	ECR-15-003371	04MAR2015	GSK	BvH

NOTES:
 Tolerances cable lengths:
 0m to 0.5m +30mm
 0.5m to 1.0m +50mm
 1.0m to 3.0m +100mm
 < 3.0m +1.5%



VIEW 'A'

TECHNICAL DATA	
Operating voltage	max. 30 V AC/DC
Operating current per contact	max. 4 A
Locking of ports	Screw thread M8 x 1 mm (recommended torque 0.4 Nm) self-securing
Protection	IP65 and IP67 when plugged and screwed down (EN 60529)
Temperature range	-25...+85 °C

CABLE	
No./diameter of wires	3 x 0.34 mm ²
Wire isolation	PP (br, bk, bl) (UL/CSA)
Outer diameter	approx. 2.7 mm
Bend radius (moving)	10 x outer diameter
Temperature range (fixed)	-40...+80 °C
Commercial data	

3 pos	0.2mtr	2273014-1	3X22AWG PANELMOUNT 0.2m WIRES	1
	LENGTH "L"	TE PN	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 12NOV2013 SATHISH KUMAR.G	STE TE Connectivity	
		CHK 12NOV2013 B.VELDHOVEN		
DIMENSIONS: mm		APVD 12NOV2013 A.VAN ZANDVOORT	NAME M8 MALE PANEL MLD REAR MT M8 FAST PIGT	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC 108-19483		
0 PLC ± -		APPLICATION SPEC 114-32127		
1 PLC ± -		WEIGHT -	SIZE A3	CAGE CODE 00779
2 PLC ± -			DRAWING NO C-2273014	RESTRICTED TO -
3 PLC ± -				
4 PLC ± -				
ANGLES ± -				
MATERIAL -				
FINISH -				
CUSTOMER DRAWING			SCALE NTS	SHEET 1 OF 1
			REV A1	