

SEALED SMT SUB-MINIATURE




SPECIFICATIONS

Contact Rating:	0.4 VA max. @ 20 VAC or DC max.
Electrical Life:	50,000 make-and-break cycles at full load
Contact Resistance:	20 mΩ max. initial @ 2-4 VDC 100 mA
Insulation Resistance:	10 ⁹ ohm min.
Dielectric Strength:	1,000 V RMS @ sea level
Operating Temperature:	-30° C to 85° C
Packaging:	Tape & Reel

MATERIALS


Case & Bushing:	High temp material, glass filled 4/6 Nylon, flame retardant, heat stabilized (UL94-V0)
Actuator:	Brass, chrome plated with internal O-ring seal standard
Switch Support:	Brass/Steel, tin or tin-lead plated
Contacts / Terminals:	Gold plate over nickel plated copper alloy
Terminal Seal:	Epoxy

HOW TO ORDER






EXAMPLE


200B → WMSP1 → T2 → A1 → SM6 → R → E



P.C. MOUNTING



Schematic



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE.