





COIL: @ 25°C
 RESISTANCE 700 OHMS ± 10%
 NOMINAL VOLTAGE 26.5 VDC
 MUST OPERATE 14.0 VDC
 MUST RELEASE 1.8 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: DIELECTRIC 1000 VRMS EXCEPT
 500 VRMS ACROSS OPEN CONTACTS.

CUSTOMER DATA SHEET



CONTACT RATING: 10 AMP/28 VDC
 RESISTIVE 50,000 OPERATIONS

DR. R.B. 6/4/98 CK. 6/4/98

COMMUNICATIONS
 INSTRUMENTS, INC.

CUST. C. I. I. STD.
 CUST. NO.

TYPE *CBW* RELAY

CBW-1C-24B